
Delphi | E25171-CHK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Long spans of fluted concrete panels blend Western classicism with modern technology. Scalloped concrete is finished in a Chalky White finish and suitable for damp locations. Choose from stem hung pendants or backlit wall panels that provide ambient lighting and bring tranquility to spaces.



MEASUREMENTS

DIMENSION	: 8.75" L x 8.75" W x 6.25" H x 1.75" Ext
MAX OAH	: 3.93" W x 0.59" H
HANGING WEIGHT	: 2.6 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 500 Rated (480 Del.)
BULB	: 1 x 6W LED DC Integrated , 6W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Up/Down

FINISHES OPTION

Chaulk White (CHK)

MATERIAL

Concrete, Steel, PC

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Up/Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

PHOTOMETIC: Report Found Online

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com