

KINDLE

RTL4715-PBR/SSD

Designed for life in motion, Kindle is a versatile rechargeable lamp with a vintage-inspired silhouette. A Soft Sand shade, etched clear glass, and Patina Brass details lend a warm, artisanal presence, while the carry handle adds function and charm. At 14.5" high, it's perfectly sized to move effortlessly from room to garden—bringing light wherever it's needed most.

FINISHES

PATINA BRASS w/ SOFT SAND

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 14.5"

Width/Diameter: 11.75"

Canopy/Backplate: 3.5"

Product Weight: 3lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Clear Spot Etched

Shade 1 Top Width: 4.75"

Shade 1 Height: 6.75"

ELECTRICAL



Bulb 1

Bulb Included: N/A

Socket: Integrated LED

Max Wattage: 3

Bulb Quantity: 1

Wire Length: 60"

Cord Type: BLACK FABRIC USB-C CHARGING
CORD

Switch Type: TOUCH DIMMER

Gem Box Required (2"x3"): No

Dark Sky: No

CRI: 90

Color Temp.: 2700k

Lumens: 50

Title 24: No

Field Serviceable: No



Battery

Battery Powered: Yes

Battery Included: Yes

Battery Life: 12-15 Hours

SHIPPING

Carton 1: 15" x 15" x 11"

Carton 1 Weight: 4lb

Shipping Method: Ground

Country of Origin: VN

HUDSON VALLEY
LIGHTING GROUP

| hvlgroup.com | 1.800.814.3993