Allumettes | E23347-122GLD


Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION



MEASUREMENTS

DIMENSION	: 8.5" L x 8.5" W x 41" H
MAX OAH	: 84.5" OAH
CANOPY	: 5.5" W x 1.75" H x 5.5" L
HANGING WEIGHT	: 16 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 1,500 Rated (1,200 Del.)
BULB	: 12 x 3W LED PCB Integrated , 36W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: TriacÂ orÂ ELVÂ atÂ 120V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Black (BK)

Gold (GLD)

GLASS

Clear Crystal 122

MATERIAL

Steel, Crystal

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 30000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com