Alto | E23452-SN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION

Alto brings clean utility and refined detail to bath lighting with a full-length backplate and softly diffused Matte White acrylic lens. The streamlined form delivers even LED illumination while offering a polished solution for both residential and commercial spaces. Its extended backplate adds visual presence and simplifies remodel installations where broader coverage is helpful. Available in Satin Nickel, Polished Chrome, and Black, Alto coordinates easily with common bath hardware. A 5CCT selectable switch allows the color temperature to adjust from warm 2700K to crisp 5000K for flexible project needs.

MEASUREMENTS

DIMENSION	: 5" W x 24" H x 3" Ext
BACK PLATE	: 5" W x 24" H x 12" HCO
HANGING WEIGHT	: 4.18 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,200 Rated (2,100 Del.)
BULB	: 1 x 20W LED AC Integrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: All

FINISHES OPTION

Black (BK)
Polished Chrome (PC)
Satin Nickel (SN)

MATERIAL

Aluminum, Steel, PC

RATINGS

cETLus
Damp Location
CA Title 24
ADA

ADDITIONAL

INSTALL UP/DOWN: Vertical/Horizo
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com