



Ortronics
Clarity Cat6a TracJack, T568A/B, 8 pos, Yellow 180 degree
Part No. TJ6A-44



Clarity 6a, 6 & 5e TracJacks, ETL verified to TIA Category 6a, 6 & 5e component specification. Front-loading and front removable. New universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned to Clarity patch cords for optimum performance.

TracJack® modules combine the ease and reliability of a front-loading individual jack with 110 termination.

Features & Benefits

ETL Verified to Category 6A component standard
Ensures standards compliance.

Center tuned design
Transparent interface with Clarity 6A/10G cords

Standard TracJack footprint
Fits in all TracJack faceplates and housings

Easy to follow universal wiring label
Quick and user-friendly, eliminates confusion.

Easy lace IDC housing
Reduces wiring time

Icon compatible, C6A marking on jack face
Supports 606 designation requirements

Specifications

General Info

Product Line	Ortronics	UPC Number	662875855569
Country Of Origin	Mexico	Application Sector	Commercial/Industrial
Standard	TIA-568.2-D, UL 1863, IEEE 802.3af / 802.3at, 802.3bt Type 3 and Type 4, FCC part 68, Subpart F and IEC-603-7 compliant	Type	Jack

Additional Information

RoHS Conformant Yes

Technical Information

Category Performance Rating Cat 6a Shielded/Unshielded Unshielded

Temperature Rating

-10°C to 60°C

Connector Type

RJ45

Performance Level/Tier

Cat 6a
