



TEGERA® INFINITY 8804

Learn more

FULLY DIPPED, DOUBLE COATED PALM

Precision work glove with a unique feeling and high dexterity for jobs in greasy and oily environments. Ultra light thanks to 18 gg knitting. Fully dipped with microfoam coated palm for better grip performance. Withstands contact heat up to 100°C/212°F. Anatomically designed, passes Derma-tests and has Oeko-Tex certificate.

CHARACTERISTICS

- Extremely good fingertip sensitivity
- Extra flexible
- Durable
- Good grip
- Extra comfortable

FUNCTIONS

- Withstands contact heat up to 100°C
- Approved for handling foodstuffs
- Oil and grease resistant
- Thin

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

PREVENTS RISK OF

Abrasion injuries, Blisters, Grazes, Scratches, lacerations, Contact with dirt, Chapping, Contact with moisture, Contact with oil and fat

PRIMARY ENVIRONMENTS OF USE

Moist environments, Oily and greasy environments, Dirty environments

PRIMARY AREAS OF USE

Fine assembly, Assembly, Machine operating, Building and construction, Carpentry, Installation work, HVAC installation, Engineering, Transport work, Machine driving, Warehouse work, Airport work, Repair work, Service work, Shop work

PRIMARY INDUSTRIES OF USE

Agriculture, forestry and fishing, Automotive manufacturing, Automotive repair and maintenance, Basic metals manufacturing, Building and construction, Electrical equipment manufacturing, Electricity and gas supply, Facility management services, Machinery and equipment manufacturing, Metal manufacturing and fabrication, Mining and quarrying, Public safety, security and defence, Retail and wholesale, Transport equipment manufacturing, Transportation and logistics, Warehousing

TYPE OF WORK

Light weight

SPECIFICATION

TYPE Heat protection gloves, Precision work gloves
CATEGORY Cat. II
COLLECTION Infinity
KNITTING GAUGE (GG) 18
LINING MATERIAL Nylon, Spandex
LENGTH 220-270 mm
DEXTERITY 5
GRIP DESIGN Foam grip pattern
COLOUR Black
PAIRS PER: BUNDLE/CARTON 6/120
DISPLAY TYPE Bulk pack
DIPPING Fully dipped
DIPPING MATERIAL Nitrile, Nitrile foam, Waterbased PU
CUFF STYLE Knitwrist cuff
CUFF MATERIAL Textile
CUT RESISTANCE (EN ISO 13997) Cut resistance level A
CUT RESISTANCE (EN ISO 13997) TDM: 1.3 N
INNER MATERIAL SPECIFICATION Nylon, Elastane
OUTER MATERIAL SPECIFICATION Nitrile

COMPLIANCE

CE Cat. II
TP TC 019:2011

UKCA Cat. II
EN ISO 21420:2020

EAC

EN 388:2016+A1:2018 4121A

EN 407:2020 (No flame protection) X1XXXX

ANSI 4 ABR

Contact heat rating valid for palm area only

SIZE		ARTICLE NUMBER	EAN
6	XS	8804-6	7340118383774
7	S	8804-7	7340118319179
8	M	8804-8	7340118319186
9	L	8804-9	7340118319193
10	XL	8804-10	7340118319155
11	XXL	8804-11	7340118319162

ejendals
Limavägen 28, SE-793 32 Leksand, Sweden
Phone +46 (0) 247 360 00 | info@ejendals.com | order@ejendals.com

All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.