
Embosse | E22794-PBZ

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Simple and elegant LED surface mounts in archetypal shapes can be used on walls as lighted mirrors or blend seamlessly as a coordinating detail of a bathroom mirror providing enough light output to effectively illuminate a vanity space. Considering a different approach to this concept, these LED surface mounts are also produced with a warmer, Bronze tinted mirror adding an element of moodiness and drama to the reflective surface. The result is a transformation of the overall ambience that opens the design up to additional install applications.



MEASUREMENTS

DIMENSION	: 24" W x 7" H x 1.75" Ext
BACK PLATE	: 23.75" W x 6.75" H x 12" HCO
HANGING WEIGHT	: 27.2 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 3,600 Rated (790 Del.)
BULB	: 1 x 36W LED PCB Integrated , 36W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: CCT Select 5KK
LIGHTING_DIRECTION	: Backlit

FINISHES OPTION

Polished Bronze (PBZ)

Polished Chrome (PC)

MATERIAL

Steel, Stainless Steel, Acrylic

RATINGS

cETLus
Damp Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Horizontal/Vert
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com