Interlace | E30292-ACPBK

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

An Antique Copper grid constructed of 304 Grade Stainless Steel is framed along an integrated LED light source. The woven pattern of this grill is both elegant and adds an elegant element to the minimal design. Backlit along its sides the LED light highlights the pattern formed accentuating the design's most exemplary feature.



MEASUREMENTS

DIMENSION	: 6.5" W x 24" H x 2.75" Ext
BACK PLATE	: 4" W x 7.75" H x 12" HCO
HANGING WEIGHT	: 31 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,540 Rated (990 Del.)
BULB	: 2 x 11W LED AC Integrated , 22W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV
CRI	: 90 CRI
COLOR_TEMP	: 3000K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Black/Aged Copper (ACPBK)

MATERIAL

Aluminum, 314 Stainless Steel

RATINGS

cETLus
Wet Location
ADA

ADDITIONAL

INSTALL UP/DOWN: Any
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com