







CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET QTY	NJ	TX	IL	CA	GA	COO
LED Emergency Light - SEL17											
 SEL17	LED EM, WHITE PLASTIC HOUSING, NICAD BATTERY, 17FT	080083722143	1.4	6	270	•	•	•	•	•	CN
SEL17BK	LED EMERGENCY LIGHT, 17 FEET COVERAGE, NICAD BATTERY, BLACK FINISH	080083808861	1.4	6	270				•	•	CN
LED Emergency Light - SEL25, SEL50, SEL60											
 SEL25	LED EM, WHITE PLASTIC HOUSING, NICAD BATTERY, 25FT	080083736669	1.8	6	270	•	•	•	•	•	CN
SEL25BKSD	LED EMERGENCY LIGHT, 25 FEET COVERAGE, NICAD BATTERY, BLACK FINISH, SELF-DIAGNOSTIC	080083723041	1.8	6	270					•	MX
SEL25SD	LED EM, WHITE PLASTIC HOUSING, NICAD BATTERY, SD, 25FT	080083723027	1.8	6	324			•		•	CN
SEL25SDSQ	LED EMERGENCY LIGHT, 25 FEET COVERAGE, NICAD BATTERY, WHITE FINISH, SELF-DIAGNOSTIC, SQUARE SHAPE	080083780709	1.7	6	270					•	CN
SEL25R10SD	LED OUTDOOR EMERGENCY LIGHT - 25 FEET OF COVERAGE - WHITE - 10W REMOTE - SD	080083733545	3.3	6	216					•	CN
SEL25R16SD	LED OUTDOOR EMERGENCY LIGHT - 25 FEET OF COVERAGE - WHITE - 16W REMOTE - SD	080083787074	2.2	6	270					•	CN
SEL50	LED M, WHITE PLASTIC HOUSING, NICAD BATTERY, 50FT	080083733347	2.2	6	324	•		•		•	CN
SEL50SD	LED EM, WHITE POLYCARBONATE, NICAD BAT, 50 FT, SD	080083733361	1.7	6	270	•		•		•	CN
SEL50R14SD	LED OUTDOOR EMERGENCY LIGHT - 50 FEET OF COVERAGE - WHITE - 14W REMOTE - SD	080083770588	2.2	6	270					•	CN
SEL60R4	LED OUTDOOR EMERGENCY LIGHT - 60 FEET OF COVERAGE - WHITE - REMOTE	080083733422	3.3	6	216			•		•	CN
SEL60R4SD	LED OUTDOOR EMERGENCY LIGHT - 60 FEET OF COVERAGE - WHITE - REMOTE - SD	080083733446	1.7	6	270					•	CN
SEL60R10SD	LED OUTDOOR EMERGENCY LIGHT - 60 FEET OF COVERAGE - WHITE - 10W REMOTE - SD	080083770595	2.2	6	270					•	CN
SEL50BKSD	LED EMERGENCY LIGHT, 50 FEET COVERAGE, NICAD BATTERY, BLACK FINISH, SELF-DIAGNOSTIC	080083733408	2.2	6	324					•	CN
SEL50R7SD	LED EMERGENCY LIGHT, 50 FEET COVERAGE, NICAD BATTERY, WHITE FINISH, SELF-DIAGNOSTIC, 7 WATT REMOTE CAPACITY	080083733620	1.7	6	270					•	CN
SEL50SDSQ	LED EMERGENCY LIGHT, 50 FEET COVERAGE, NICAD BATTERY, WHITE FINISH, SELF-DIAGNOSTIC, SQUARE SHAPE	080083780730	1.7	6	270					•	CN
SEL60R4BKSD	LED EMERGENCY LIGHT, 60 FEET COVERAGE, NICAD BATTERY, BLACK FINISH, SELF-DIAGNOSTIC, 4 WATT REMOTE CAPACITY	080083733460	1.7	6	270					•	CN
LED Emergency Light - SELA											
SELA29SD	SELA EMERGENCY LIGHT, 120V/277V, 29FT, SELF-DIAGNOSTIC, WHITE	080083807161	2.33	6	96					•	CN
SELA29BKSD	SELA EMERGENCY LIGHT, 120V/277V, 29FT, SELF-DIAGNOSTIC, BLACK	080083807192	2.33	6	96					•	CN
 Steel Housing - HR	HR12117	EMERGENCY LIGHT 9W, 120/277VAC, 12VDC, WHITE SURE-LITES	662401474882	25.75	1	54				•	MX
Emergency Architectural											
Die Cast Aluminum Housing - AEL231, AEL246											
 AEL231SD	ARCHITECTURAL EMERGENCY LIGHT, LED, 3100K, SILVER, SELF-DIAGNOSTICS	080083681266	1.13	4	144					•	CN
AEL246SD	ARCHITECTURAL EMERGENCY LIGHT, LED, 4600K, SILVER, SELF-DIAGNOSTICS	080083679751	1.13	4	144					•	CN
Die Cast Aluminum Housing - AEL231BK, AEL246BK											
 AEL231BKSD	ARCHITECTURAL EMERGENCY LIGHT, LED, 3100K, BLACK, SELF-DIAGNOSTICS	080083679706	1.13	4	144					•	CN
AEL246BKSD	ARCHITECTURAL EMERGENCY LIGHT, LED, 4600K, BLACK, SELF-DIAGNOSTICS	080083679737	1.13	4	144					•	CN
Die Cast Aluminum Housing - AEL231BZ, AEL246BZ											
 AEL231BZSD	ARCHITECTURAL EMERGENCY LIGHT, LED 3100K, BRONZE, SELF-DIAGNOSTICS	080083679713	1.13	4	144					•	CN
AEL246BZSD	ARCHITECTURAL EMERGENCY LIGHT, LED, 4600K, BRONZE, SELF-DIAGNOSTICS	080083679744	1.13	4	144					•	CN

Ⓢ Indicates EISA Compliant Pulse Start Products Indicates MarketPro Product Country of Origin - as Indicated

Please reference the Cooper Lighting Stock Guide Terms and Conditions page. Pictures are a representation of product categories and may not illustrate the exact skus listed. Product information is subject to change without notice. Consult factory representative for additional information and inventory details. Visit www.cooperlighting.com for more product information.