

Nextrema® Schott

Nextrema Schott glass ensures even heat distribution and minimizes light emissions.

Ease of Operation

Programmable timer with remote control, features safety shutoff after 8 hours of continuous operation.

Outdoor Rated

Water/dust tight IP65 rating for outdoor applications.



Model	Watts	Volts	Length (in/cm)	Weight (lbs./kg)
DIR15A10GR	1500	120	35-1/2 / 90.1	13.4 / 6.1
DIR18A10GR	1800	240	35-1/2 / 90.1	13.4 / 6.1
DIR22A10GR	2200	240	35-1/2 / 90.1	13.4 / 6.1

Height x Depth
6-3/4" x 3"
17.1 cm x 7.6 cm



Model	Watts	Volts	Length (in/cm)	Weight (lbs./kg)
DIR30A10GR	3000	240	50-5/8 / 128.6	18.4 / 8.4

Height x Depth
6-3/4" x 5"
17.1 cm x 12.8 cm