
MASTER®
THE PROFESSIONAL'S CHOICE SINCE 1953


Master MAC-30WOSC 30" High Velocity Oscillating Wall Fan 7550 CFM, 1/4 HP, 120 Volt



- Perfect for the garage, barn, patio or workshop
- All-metal construction for durability
- Direct-drive motor with high airflow, up to 7550 CFM
- Oscillating fan head for directional airflow contro
- Wall mount included
- 1-year limited warranty

Product Description

When you need to cool down quickly, look no further than Master's industry-leading 30" High Velocity Oscillating Wall Fan. The heat of summer is no match for its powerful, direct-drive motor and long-lasting all-metal construction. Plus, the tilt-angle head lets you direct the airflow wherever it is most convenient. Whether you're in the barn, relaxing on the patio, or working in the garage, this fan will do the job while giving your A/C and wallet a rest. ***Master – built for power.***



©2026 Pinnacle Climate Technologies

Features and Benefits

- Great for your home, garage, barn, or workshop
- All-metal construction for durability
- Direct-drive motor with airflow up to 7550 CFM
- 1/4 HP industrial motor
- Oscillating fan head for directional airflow control
- All-metal safety guard
- Wall mount included
- 3 variable speed settings for user preference
- Balanced blades for optimal airflow
- 1-year limited warranty

Key Specs

Model Number	MAC-30WOSC
Brand	Master
Warranty	1-year limited warranty
Net Weight (lb.)	43
Air Flow (CFM)	7550 / 6800 / 5800
Motor Size (HP)	1/4
Variable Speed	Yes
Volts	120
Amps	1.7
Product Dimensions (L x W x H) (in.)	32 x 10 x 32

Master is a registered trademark of Pinnacle Climate Technologies, Inc.

©2026 Pinnacle Climate Technologies