



Project / Job Name: _____

Location: _____

Fixture Type: _____

Notes: _____

65-1173 - 320/295/255 Watt LED Linear High Bay;
3K/4K/5K CCT; IP69K; 120-347 Volt; White Finish



GENERAL

Company	NUVO
EA Height	3.94
EA Width	15.55
EA Length	25.0
Bulb Included	Integrated
Chain Length (in)	41
Dimmable Text	0-10V Dimming
Material	Aluminum
Fixture Type	Linear Hi-Bay
Status	Active
Surge Protection	Built-in surge protection - 6KV
Total Harmonic Distortion	<20%
CCT Selectable	Yes
Wattage Selectable	Yes
Finish Family	White
Additional Info	Default Wattage: 320W
Amps	2.670-0.920/2.460-0.850/1.880-0.650A
Integrated Features	Integrated Sensor Port
Lens Finish	Opaque
Lens Material	Polycarbonate (PC)
Lensed	Yes
Power Factor	>0.9
SDS Class	LED_Fixture
Product Technology	LED
Fluor Equiv	545W-760W

ELECTRICAL

CCT (Kelvin Temp)	3000K/4000K/5000K
Dimmable	Yes-Dimmable
Hours Rated	50000
Beam Angle (degree)	90
Color Temp	Soft White to Natural Light
CRI	80+
Dimming Type	0-10V Dimming
Operating Frequency	50/60Hz
Operating Temp	-40C (-40F) to +55C (+131F)
HID Equivalent	550W
Lumens	51000L-36700L
Volts	120V-347V
Watts	320W/295W/255W

PHYSICAL

Finish	WHITE
Housing Color	White

ADDITIONAL INFO

Warranty	5-Years
----------	---------

PACKAGING

UPC	045923413285
Case Cube	0.8864
Case Height	3.94
Case Length	25.0
Case Quantity	1
Case UPC	10045923413282
Case Weight	18.7
Case Width	15.55
EA Cube	0.8864
EA Height	3.94
EA Length	25.0
EA Quantity	1
EA Weight	18.7
EA Width	15.55
Pack Type	Box
Web Height	2.44
Web Length	24.21
Web Width	14.76

COMPLIANCE

Bug Rating	B4-U2-G2
CA Prop 65	Lead
DLC ID	S-PQLQMV
FCC Compliant	Yes
IP Rating	IP69K
Location Rating	Wet
NSF Approved	Yes
ROHS Compliant	Yes
Safety Listing	cULus - Certified
California Ban	Lawful for sale
DLC Approved	Yes
Title 20	Exempt
T24 Compliant	No