





PRODUCT DESCRIPTION

Kaia brings the warmth of natural texture to outdoor living with a clean, modern ring of light. Hand-wrapped synthetic rattan surrounds the LED frame, softening the architectural form with a relaxed, furniture-inspired character. Offered in Natural or Grey tones, the finish coordinates beautifully with outdoor furnishings while non-corrosive construction and damp-rated performance make it suited for covered exterior spaces. Available as a 20" flush mount and 36" or 48" pendants, Kaia delivers ambient illumination with selectable CCT flexibility for patios, lounges, and open-air gathering areas.

MEASUREMENTS

DIMENSION	: 48.25" L x 48.25" W x 2.5" H
MAX OAH	: 124.25" OAH
CANOPY	: 8.25" W x 1.75" H x 8.25" L
HANGING WEIGHT	: 8.2 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 6,400 Rated (4,000 Del.)
BULB	: 1 x 80W LED DC Integrated , 80W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Triac or ELV at 120V
CRI	: 90 CRI
COLOR_TEMP	: 22-27-30-35-40K

FINISHES OPTION

Antique Bronze (ANB)

Gray (GY)

MATERIAL

Steel,Acrylic, Rattan

RATINGS

cETLus
Damp Location

ADDITIONAL

RATED LIFE 40000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com