



Technical Data

Color	Blue, Yellow, White, Dark Blue, Hi-Vis Orange, Red, Gray, Green, Orange, Black
Sizes Available	OS
Packaging	Bagged Each
Packed	20/Case
Case Dimensions (in)	23.00 x 19.00 x 23.00
Case Weight (lbs)	22.99
Country of Origin	Mexico
Shell Material	HDPE
Shell	Non-Vented
Brim Style	Cap Style
Brim Length	Standard
Size Adjustment	Wheel Ratchet
Certifications	ANSI/ISEA Z89.1, TAA Compliant

Performance Data

ANSI Type	Type I
Electrical Class	Class C

Fibre-Metal® E2

Type I, Non-Vented, Cap-Style Smooth Dome Hard Hat with Heat Resistant Thermoplastic HDPE Shell, 8-Point SuperEight™ Suspension and Wheel Ratchet Adjustment, Includes Quick-Lok® Accessory

- Thermoplastic design withstands high temperatures, making it suitable for use in demanding environments
- 360° padded sweatband provides exceptional comfort
- Ratchet headband ensures head-hugging stability and easy adjustment
- Smooth crown design contains a technically advanced SuperEight™ suspension with 8 load-bearing points to stabilize and balance the hard hat
- Quick-Lok pre-assembled on hard hat
- Meets ANSI/ISEA Z89.1, Type I, Class C requirements

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
E2QRW11A000	Black	OS	662463223183		30662463223184
E2QRW71A000	Blue	OS	662463223091		30662463223092
E2QRW75A000	Dark Blue	OS	662463223190		30662463223191
E2QRW09A000	Gray	OS	662463223169		30662463223160
E2QRW74A000	Green	OS	662463223060		30662463223061
E2QRW46A000	Hi-Vis Orange	OS	662463484232		30662463484233
E2QRW03A000	Orange	OS	662463223114		30662463223115
E2QRW15A000	Red	OS	662463223046		30662463223047
E2QRW01A000	White	OS	662463223015		30662463223016
E2QRW02A000	Yellow	OS	662463223022		30662463223023