

Valves Product



True Union 2000 Industrial Ball Valves

CPVC Industrial

Size	EPDM	FKM	Std Pk	Mstr Pk	Prod Code
Threaded & Socket Ends					
1/2	1829-005C	1839-005C	1	18	602
3/4	1829-007C	1839-007C	1	18	602
1	1829-010C	1839-010C	1	12	602
1-1/4	1829-012C	1839-012C	1	8	602
1-1/2	1829-015C	1839-015C	1	8	602
2	1829-020C	1839-020C	1	4	602

Socket Ends

2-1/2	1822-025C	1832-025C	1	0	603
3	1822-030C	1832-030C	1	0	603
4	1822-040C	1832-040C	1	0	603
6	1822-060C	1832-060C	1	0	613
8	1822-080C	1832-080C	1	0	613

8" Venturied valves are 6" ball valves fitted with 6x8 end connector adapters.

Threaded Ends

2-1/2	1821-025C	1831-025C	1	0	603
3	1821-030C	1831-030C	1	0	603
4	1821-040C	1831-040C	1	0	603
6	1821-060C	1831-060C	1	0	613

SR Threaded Ends

1/2	1821-005CSR	1831-005CSR	1	18	602
3/4	1821-007CSR	1831-007CSR	1	18	602
1	1821-010CSR	1831-010CSR	1	12	602
1-1/4	1821-012CSR	1831-012CSR	1	8	602
1-1/2	1821-015CSR	1831-015CSR	1	8	602
2	1821-020CSR	1831-020CSR	1	4	602
2-1/2	1821-025CSR	1831-025CSR	1	0	603
3	1821-030CSR	1831-030CSR	1	0	603
4	1821-040CSR	1831-040CSR	1	0	603
6	1821-060CSR	1831-060CSR	1	0	613

Spigot Ends

1/2	1827-005C	1837-005C	1	18	602
3/4	1827-007C	1837-007C	1	18	602
1	1827-010C	1837-010C	1	12	602
1-1/4	1827-012C	1837-012C	1	8	602
1-1/2	1827-015C	1837-015C	1	8	602
2	1827-020C	1837-020C	1	4	602
2-1/2	1827-025C	1837-025C	1	0	603
3	1827-030C	1837-030C	1	0	603
4	1827-040C	1837-040C	1	0	603
6	1827-060C	1837-060C	1	0	613

Flanged Ends

1/2	1823-005C	1833-005C	1	8	602
3/4	1823-007C	1833-007C	1	8	602
1	1823-010C	1833-010C	1	8	602
1-1/4	1823-012C	1833-012C	1	8	602
1-1/2	1823-015C	1833-015C	1	4	602
2	1823-020C	1833-020C	1	0	602
2-1/2	1823-025C	1833-025C	1	0	603
3	1823-030C	1833-030C	1	0	603
4	1823-040C	1833-040C	1	0	603
6	1823-060C	1833-060C	1	0	613

CPVC Industrial (continued)

Size	EPDM	FKM	Std Pk	Mstr Pk	Prod Code
------	------	-----	--------	---------	-----------

Flanged Ends

8	1823-080C	1833-080C	1	0	613
---	-----------	-----------	---	---	-----

8" Venturied valves are 6" ball valves fitted with 6x8 end connector adapters.

CPVC 6" Industrial T-Handle Valve Option (Non-Locking)

NOTICE: T-Handle is more compact, but will greatly increase difficulty of operation.

Size	EPDM	FKM	Std Pk	Mstr Pk	Prod Code
------	------	-----	--------	---------	-----------

Socket Ends

6	18226-060C	18326-060C	1	0	613
---	------------	------------	---	---	-----

Threaded Ends

6	18216-060C	18316-060C	1	0	613
---	------------	------------	---	---	-----

SR Threaded Ends

6	18216-060CSR	18316-060CSR	1	0	613
---	--------------	--------------	---	---	-----

Flanged Ends

6	18236-060C	18336-060C	1	0	613
---	------------	------------	---	---	-----

True Union 2000 Industrial Vented/Bleach Ball Valves



Pressure Rating @ 73°F (23°C), Water

1/2" - 4"	235 psi
6"	150 psi
Flanged	150 psi

Same True Union 2000 Industrial Ball Valve with Special Ball Vent Design for Sodium Hypochlorite (Bleach) and other Chemical Applications where entrapped fluids may form caustic crystalline residues and pressure build up from gases developed. Valve has a 1/8" vent hole in ball to equalize internal fluid pressures. Install valve with ball vent on the pressure (upstream) side when in closed position.

All Valves assembled with Silicone-Free, Water Soluble Lubricant

Contact Spears® for MSRP & Availability on Custom Elastomer Seals. See Ball Valve Accessories & Repair Kits Section for Additional Options and Features

PVC True Union 2000 Industrial Vented/Bleach Ball Valves

Size	EPDM	FKM	Std Pk	Mstr Pk	Prod Code
------	------	-----	--------	---------	-----------

Threaded & Socket Ends

1/2	1829V-005	1839V-005	1	18	600
3/4	1829V-007	1839V-007	1	18	600

Made in the U.S.A.

Suitable for Oil-Free air handling to 25 psi, not for distribution of compressed air or gas
See MSRP-1 Sheet or Check Spears® On-line Catalog @ www.spearsmfg.com for Pricing

Page 24