Soprano | E23412-01PC

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____







PRODUCT DESCRIPTION

Hitting a high note with an affordable solution for LED bath vanities, the Soprano series features an Satin White glass tube supported on a streamlined aluminum extrusion finished in Polished Chrome. On its backside, a dip-switch allows you to select between 5 color temperatures to allow simple changes from a relaxingly warm 2700k to more neutral white lighting temperatures and up to a daylight white of 5000k. Convenient and clean, this LED bath bar is an easy choice to update a bathroom.



MEASUREMENTS

DIMENSION	: 24" L x 4.75" W 3.5" Ext
BACK PLATE	: 4.75" W x 4.75" H x 2.5" HCO
HANGING WEIGHT	: 1.1 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 1,400 Rated (1,200 Del.)
BULB	: 1 x 18W LED PCB Integrated , 20W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Y
CRI	: 90 CRI
COLOR_TEMP	: 27-30-35-40-50K
LIGHTING_DIRECTION	: Omni

FINISHES OPTION

Polished Chrome (PC)

GLASS

White 01

MATERIAL

Metal+Glass

RATINGS

cETLus
Damp Location

ADDITIONAL

INSTALL UP/DOWN: Horiz/Vert
RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com