# **Unity** | E24613-BCN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








## PRODUCT DESCRIPTION

Abstract shapes of stainless steel are finished in Brushed Champagne or Black Chrome and intersect to create an intriguing sculpture of light. Unity provides both art and illumination for those searching for a unique lighting piece.




*Height from center of outlet to the top of the fixture

### MEASUREMENTS

| | |
|---|---|
| DIMENSION | : 8" W x 27.25" H x 10.5" Ext |
| MAX OAH | : 4.75" W x 4.75" H |
| HANGING WEIGHT | : 4.18 lb |

### LAMPING

| | |
|---|---|
| INPUT VOLTAGE | : 120-277V |
| LUMENS | : 2,400 Rated (1,350 Del.) |
| BULB | : 3 x 10W LED DC Integrated , 30W Total |
| BULB INCLUDED | : (Integrated) |
| DIMMABLE | : 3-in-1: Triac, ELV, or 0-10V |
| CRI | : 90 CRI |
| COLOR_TEMP | : 3000K |
| LIGHTING_DIRECTION | : Down |

### FINISHES OPTION

Black Chrome (BC)

Brushed Champagne (BCN)

### MATERIAL

Stainless Steel, PC

### RATINGS

cETLus
Damp Location

### ADDITIONAL

INSTALL UP/DOWN: Down
RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com