



Ironcat®

AR Premium Grade Split Cowhide Leather Welder's Glove with Para-Aramid Cut Lining

- Split Cowhide leather construction provides comfort, durability, excellent abrasion resistance, and breathability
- Para-aramid blended lining provides 360 degree added cut and heat resistance, which extends down thru the cuff
- ARC Rating: ATPV 63 cal/cm2
- Fully welted to protect seams from abrasions
- Stitched with Kevlar® adding strength and burn resistance
- Reinforced palm and thumb strap increases durability and provides added protection at common wear points
- Wing thumb increases comfort in open-handed work
- One-piece back for extended glove life
- 14" glove length



Technical Data

Color	Blue
Sizes Available	S-2XL
Packaging	Bulk Pack
Packed	6 Dozen/Case
Case Dimensions (in)	19.02 x 16.50 x 22.01
Case Weight (lbs)	73.63
Country of Origin	Pakistan
Hide	Split Cowhide
Lining	Aramid
Grade	Premium
Cuff	Gauntlet
Length	14"
Palm	Split Cowhide
Back	Split Cowhide Leather
Closure	Slip On
Thumb	Wing
Stitching	Kevlar
Construction	Cut-and-Sewn

Performance Data

ARC Rating	63 cal/cm2
ARC Rating	63 cal/cm2
Cut Level	A4
Cut Level	A4
ANSI Puncture Level	3
ANSI Puncture Level	3

Care Instructions



Do Not Wash

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
946/S	Blue	S	616314374517	10616314374514	20616314374511
946/M	Blue	M	616314380549	10616314380546	20616314380543
946/L	Blue	L	616314380464	10616314380461	20616314380468
946/XL	Blue	XL	616314374555	10616314374552	20616314374559
946/2XL	Blue	2XL	616314380501	10616314380508	20616314380505