



EAN:	4013288230683	Size:	175x125x61 mm
Part number:	05075840001	Weight:	436 g
Article number:	7510/14	Country of origin:	CZ
		Customs tariff number:	82041100

- Particularly suitable for bolting carbide inserts
- Torque screwdriver with quick torque adjustment
- Easy and quick torque setting
- Fixed position (Torque Lock) for unlimited tightening and loosening moments
- Secure slip-over torque function for clockwise/anti-clockwise torque-control
- Quick and easy setting of the selectable tightening torques (1.0; 1.5; 2.0; 2.5; 3.0 Nm)
- For bits with 1/4" external hexagon drive, also suitable for socket wrench inserts via adapter
- Tools with Hex-Plus profile prevent premature rounding of hexagonal socket screws

14-piece tool set. For professional screwdriving/professional fine adjustment AND for torque-controlled screwdriving. Secure slip-over torque mechanism with quick clockwise/counterclockwise setting and five selectable tightening torques (1.0; 1.5; 2.0; 2.5; 3.0 Nm) and one fixed position (Torque Lock) for unlimited loosening and tightening moments. Quick-release holder for high robustness; suitable for bits with 1/4" external hexagon drive. 14 tough bits (25 mm length) for TORX PLUS®, TORX® and hexagonal socket screws. The tool set is particularly suitable for bolting carbide inserts. The Safe-Torque Speed 7510 torque wrench with its five selectable torque values recommended by leading carbide tool manufacturers ensures a reliable torque-controlled screw connection of replaceable carbide inserts.



Web link

<https://www.wera.de/en/05075840001>

Wera - 7510/14
05075840001 - 4013288230683

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de

For bolting carbide inserts



Torque screwdriver with quick torque adjustment



The tool set is particularly suitable for bolting carbide inserts. The Safe-Torque Speed 7510 torque wrench with its five selectable torque values recommended by leading carbide tool manufacturers ensures a reliable torque-controlled screw connection of replaceable carbide inserts.

Five selectable tightening torques




Five selectable tightening torques (1.0; 1.5; 2.0; 2.5; 3.0 Nm) and one fixed position (Torque Lock) for unlimited tightening and loosening moments.

Setting with Speed



Rapid setting of the selectable tightening torques.

Excess-load signal




Distinctly audible and noticeable excess-load signal when the pre-set torque is reached.

Storage and transport



Storage and transport in a robust and compact textile roll pouch, so the tool is always close at hand.

Flexible due to hook-and-loop fastener strips



The textile box features a fleece zone at the back. Using the provided self-adhesive hook-and-loop fastener strips, the textile box can be attached to the Wera 2go components. Or to the wall, shelf or workshop trolley.

Web link

<https://www.wera.de/en/05075840001>

Wera - 7510/14

05075840001 - 4013288230683

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de

Set contents:

7510 Kraftform Safe-Torque Speed Torque screwdriver, 1-3 Nm, 1/4" x 1.0 Nm x 1.5 Nm x 2.0 Nm x 2.5 Nm x 3.0 Nm x 147.5 mm

05075810001

1x 1/4" x 1.0 Nm x 1.5 Nm x 2.0 Nm x 2.5 Nm x 3.0 Nm x 147.5 mm



867/1 IP TORX PLUS® bits, 7 IP x 25 mm

05066276001

1x 7 IP x 25 mm

05066278001

1x 8 IP x 25 mm

05066279001

1x 9 IP x 25 mm

05066280001

1x 10 IP x 25 mm

05066282001

1x 15 IP x 25 mm



867/1 TORX® bits, TX 7 x 25 mm

05066494001

1x TX 7 x 25 mm

05066495001

1x TX 8 x 25 mm

05066496001

1x TX 9 x 25 mm

05066485001

1x TX 10 x 25 mm

05066486001

1x TX 15 x 25 mm



840/1 Z bits, 2 x 25 mm

05056305001

1x 2 x 25 mm

05056310001

1x 2.5 x 25 mm

05056315001

1x 3 x 25 mm



Web link

<https://www.wera.de/en/05075840001>

Wera - 7510/14

05075840001 - 4013288230683

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: info@wera.de