

COSTA BRAVA

513-24-VGL

FINISHES

VINTAGE GOLD LEAF

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 22.5"

Width/Diameter: 24"

Minimum Height: 27"

Maximum Height: 98.75"

Canopy/Backplate: 6"

Hanging Type: 72" Chain

Product Weight: 17.6lb

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: Yes

Living Finish: No

Uplight Only: No

Shade

Shade 1: Natural Woven

Shade 1 Finish: Natural Linen

Shade 1 Top Width: 7.75"

Shade 1 Height: 16.75"

Shade 2: Natural Woven

Shade 2 Finish: Coco Beads

Shade 2 Top Width: 8"

Shade 2 Height: 18"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: B11

Max Wattage: 10

Bulb Quantity: 5

Bulb Included: No

Wire Length: 144"

Cord Type: SPT-1 SILVER W/ TINNED GROUND
WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 28" x 22" x 23"

Carton 1 Weight: 32lb

Shipping Method: Ground

Country of Origin: PH

