SATCO | NUVO

Project / Job Name:

Location:

Fixture Type:

Notes:



**65-637** - Square LED; Wide Beam Angle Canopy Light; 3K/4K/5K CCT Selectable; 60W/75W/90W Wattage Selectable; Bronze Finish

WET LOCATION · DIMMABLE · FC · RoHS COMPLIANT · CCT SELECTABLE · 50,000 HOURS · IP 65 · 0-10V DIMMING

## GENERAL

| | |
|---|---|
| Company | NUVO |
| EA Height | 11.02 |
| EA Width | 5.12 |
| EA Length | 11.02 |
| Bulb Included | Integrated |
| Material | Die-cast Aluminum |
| Fixture Type | Canopy |
| Product Notes | Multiple half-inch knockouts; Three quarter inch back knockout for pendant applications |
| Status | Active |
| Style | Utility |
| Surge Protection | Built-in surge protection - 6KV |
| Total Harmonic Distortion | <20% |
| CCT Selectable | Yes |
| Wattage Selectable | Yes |
| Finish Family | Bronze |
| Additional Info | Recommended Mounting Height: 15 to 20 Feet |
| Amps | 0.500-0.217/0.625-0.271/0.750-0.325A |
| Has Camera | No |
| Integrated Features | Integrated DC Sensor Port |
| IOT Enabled | No |
| Lens Material | Polycarbonate (PC) |
| Photo Cell | Optional Add-On |
| Power Factor | >0.9 |
| SDS Class | LED_Fixture |
| Indoor Outdoor | Outdoor |
| Product Technology | LED |
| Incandescent Equivalent | 300W |
| Serviceable Battery | No |
| Battery Indicator | No |
| Digital Display | No |

## ELECTRICAL

| | |
|---|---|
| CCT (Kelvin Temp) | 3000K/4000K/5000K |
| Dimmable | Yes-Dimmable |
| Hours Rated | 50000 |
| Beam Angle (degree) | 190 |
| Color Temp | Warm White to Natural Light |
| CRI | 80+ |
| Dimming Type | 0-10V Dimming |
| Operating Frequency | 50/60Hz |
| Operating Temp | -40F to +122F (-40C to +50C) |
| Lumens | 7920L-12557L |
| Volts | 120V-277V |
| Watts | 60W/75W/90W |
| Max Lumens | 12557L |
| Connection | Hardwire |

## PHYSICAL

| | |
|---|---|
| Lamp Base | Integrated |
| Finish | BRONZE |
| ANSI Base | Integrated |
| Lamp Type | Integrated LED |
| Fixture Shape | Square |
| Mounting Procedure | Ceiling |

## ADDITIONAL INFO

| | |
|---|---|
| Warranty | 5-Years |
| Installation Notes | Hinged door for ease of installation |

## PACKAGING

| | |
|---|---|
| UPC | 045923654206 |
| Case Cube | 1.6806 |
| Case Height | 11.81 |
| Case Length | 21.18 |
| Case Quantity | 4 |
| Case UPC | 10045923654203 |
| Case Weight | 23.32 |
| Case Width | 11.61 |
| EA Cube | 0.3598 |
| EA Height | 11.02 |
| EA Length | 11.02 |
| EA Quantity | 1 |
| EA Weight | 5.39 |
| EA Width | 5.12 |
| Pack Type | Brown Box |
| Web Height | 3.62 |
| Web Length | 9.57 |
| Web Width | 9.57 |

## COMPLIANCE

| | |
|---|---|
| Bug Rating | B3-U4-G5 |
| CA Prop 65 | Lead |
| DLC ID | S-7KZD81 |
| FCC Compliant | Yes |
| IP Rating | IP65 |
| Location Rating | Wet |
| ROHS Compliant | Yes |
| Safety Listing | cULus - Certified |
| California Ban | Lawful for sale |
| DLC Approved | Yes |
| Title 20 | Exempt |
| T24/JA8 Compliant | No |



© Satco Products, Inc.
All rights reserved 2026