Martini | E11096-10NAB

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

Class and character describe these unique LED light pendants. Start by taking a spike in Natural Aged Bass and stick it through multiple layers of glass globe shades. The outer layer is an oversized Clear glass with a slanted opening exposing a smaller White glass globe inside illuminated by the LED concealed within it. It's serving a martini and bright ideas.



*max overall height

MEASUREMENTS

DIMENSION	: 27.5" L x 23.75" W x 18.25" H
MAX OAH	: 64.25" OAH
CANOPY	: 19.75" W x 1.5" H x 19.75" L
HANGING WEIGHT	: 27.8 lb

LAMPING

INPUT VOLTAGE	: 120-277V
LUMENS	: 2,720 Rated (1,360 Del.)
BULB	: 4 x 8.5W LED DC Integrated , 34W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: 3-in-1: Triac, ELV, or 0-10V
CRI	: 90 CRI
COLOR_TEMP	: 3000K

FINISHES OPTION

Natural Aged Brass (NAB)

GLASS

Clear and White 10

MATERIAL

Glass, Steel

RATINGS

cETLus
Dry Location

ADDITIONAL

RATED LIFE 50000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com