Bevel | E42062-SN

Job Name:_____ Job Type:_____ Quantity:_____ Comments:_____








PRODUCT DESCRIPTION

White Acrylic diffusers are miter cut and beveled along the edge of these mirror frames allowing for wider, and brighter lighting. Robust in size, these mirrors feature excellent construction and 2CCT light selection using a discreet touch switch on the frames edge. Use the touch dimming switch to control the brightness and the memory function on the LED will recall the chosen color temperature of the previous setting.



MEASUREMENTS

DIMENSION	: 30" W x 36" H x 2.25" Ext
HANGING WEIGHT	: 22 lb

LAMPING

INPUT VOLTAGE	: 120V
LUMENS	: 5,300 Rated (1,800 Del.)
BULB	: 1 x 53W LED DC Integrated , 53W Total
BULB INCLUDED	: (Integrated)
DIMMABLE	: Touch Switch
CRI	: 90 CRI
COLOR_TEMP	: 3000-4000K

FINISHES OPTION

Brushed Black (BBK)

Satin Nickel (SN)

MATERIAL

Aluminum, PC , Glass

RATINGS

cETLDamp Location
ADA

ADDITIONAL

RATED LIFE 35000 Hours
OPERATING TEMPERATURE:
-20°C (-4°F), 40°C (104°F)

Always consult a qualified electrician before installing any lighting product.

ET2 Contemporary Lighting™

WESTERN DISTRIBUTION CENTER (HEADQUARTER)
253 NORTH VINELAND AVE I CITY OF INDUSTRY, CA 91746

EASTERN DISTRIBUTION CENTER
101 GARDNER PARK | PEACHTREE CITY, GA 30269

P. 626.956.4200 I F. 626.956.4225 I maximlighting.com