

LISETTE

H1092101-AGB

The Lisette family transforms simple geometric shapes into highly expressive compositions. In the 6- and 8-light semi-flush mounts, staggered arms branch outward in a radiant, bouquet-like arrangement. The 1- and 2-light sconces provide a more nuanced nod to botanical forms. Each shiny cream opal glass shade features a delicate fluted edge. Finished in Aged Brass, Lisette's dynamic energy enlivens any space.

FINISHES

AGED BRASS

Coastal Suitable Finish (EPM): No

DIMENSIONS

Height: 11.75"

Width/Diameter: 6"

Length: 6.75"

Canopy/Backplate: 4.75"

Product Weight: 3lb

Extension: 6.75"

Top to Center: 2.25"

Canopy/Backplate Shape: Round

Sloped Ceiling Compatible: No

Living Finish: No

Uplight Only: No

Shade

Shade 1: Glass

Shade 1 Finish: Cream Opal Glossy

Shade 1 Top Width: 6"

Shade 1 Height: 5.75"

ELECTRICAL



Bulb 1

Bulb Included: No

Socket: E12 Candelabra Base

Bulb Type: G16.5

Max Wattage: 10

Bulb Quantity: 1

Wire Length: 7"

Cord Type: B & W TEFLON W/ GROUND WIRE

Gem Box Required (2"x3"): No

Dark Sky: No

SHIPPING

Carton 1: 10" x 8" x 14"

Carton 1 Weight: 5lb

Shipping Method: Ground

Country of Origin: VN

