

USB-C to 3.5 mm Stereo Audio Adapter - USB 3.1 Gen 1 (5 Gbps), PD 3.0, Silver

MODEL NUMBER: U437-001-C



Connects stereo headphones or a microphone plus a USB wall charger to the USB-C port on your MacBook Pro or Windows laptop.

Features

3.5 mm Audio Adapter Connects to Your Computer's USB-C Port

This USB Type-C to Stereo Audio Adapter allows you to connect a stereo microphone, earbuds, headphones or speakers to your MacBook Pro, Windows laptop, Chromebook or other device with a USB-C port. Not only does this adapter allow you to bypass a defective sound card or 3.5 mm headphone jack, it also lets you connect to a device that offers only USB-C ports. The adapter converts digital high-resolution audio to analog to maintain a crisp, lively sound.

PD Charging Port Charges Connected Device via AC Wall Charger

The USB-C Power Delivery port supports power output up to 20V 3A (60W), which is sufficient for charging the connected source device more quickly than other chargers. Just connect the device's AC wall charger to the USB-C PD port. By connecting both the USB-C PD and 3.5 mm audio ports at the same time, you can listen to your tunes or record a podcast without using precious battery power.

Built-In USB-C Cable Attaches in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C port in either direction for a fumble-free connection every time.

Ready to Use Right Out of the Package

The plug-and-play audio adapter requires no software or external power. The compact aluminum housing fits easily into a pocket, briefcase or laptop bag for connecting on the go.

Highlights

- Adds a 3.5 mm headphone/mic port to a device that comes without a stereo audio jack
- USB-C PD 3.0 port supports 20V 3A (60W) power output for charging connected device
- Compact aluminum housing fits into a laptop bag for easy listening anywhere
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for speedy installation

Applications

- Listen to streaming music or sporting events through headphones, earbuds or speakers
- Connect a microphone to chat online via Skype or Zoom
- Record a podcast on your MacBook, Chromebook or smartphone
- Charge a smartphone, tablet or other USB-C device while making a call or listening to music

System Requirements

- Source device with USB-C port that supports USB digital audio
- Microphone, headphones, earbuds and/or speakers with 3.5 mm plug
- Windows 10, Mac OS 8.6 or



above, Linux, Chrome OS or
Android operating system

Package Includes

- U437-001-C USB-C to Stereo
Audio Adapter, Silver
- Owner's manual

Specifications

| OVERVIEW | |
|--|--------------|
| UPC Code | 037332253903 |
| INPUT | |
| Cable Length (ft.) | 0.295 |
| Cable Length (m) | 0.09 |
| Built-In Cable Length (ft.) | 0.295 |
| Built-In Cable Length (m) | 0.09 |
| Built-In Cable Length (in.) | 3.54 |
| Bus Powered | Yes |
| Product Length (in.) | 6.20 |
| Product Length (cm.) | 15.75 |
| Product Length (ft.) | 0.516 |
| Product Length (m.) | 0.157 |
| BATTERY | |
| Battery Charging (1.2 Port) | Yes |
| CHARGING | |
| Charging Ports / Amps | 3A |
| USB Power Delivery (PD) Charging Support | Yes |
| Charging Watts | 60 |
| USB Power Delivery (PD) Charging Specification | 3.0 |
| PHYSICAL | |



| | |
|---------------------------------------|-------------------------------|
| Cable Jacket Type | TPE |
| Cable Outer Diameter (OD) | 3.2 mm |
| Color | Silver |
| Material of Construction | PC + ABS, Aluminum |
| Shipping Dimensions (hwd / in.) | 0.78 x 4.72 x 3.94 |
| Shipping Weight (lbs.) | 0.79 |
| Unit Dimensions (hwd / in.) | 0.374 x 1.751 x 1.141 |
| Unit Packaging Type | Box |
| Unit Weight (kg) | 0.02 |
| Unit Weight (lbs.) | 0.05 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32 to 113 °F (0 to 45 °C) |
| Storage Temperature Range | 14 to 158 °F (-10 to 70 °C) |
| Operating Humidity Range | 10 - 85 %, RH, Non-Condensing |
| Storage Humidity Range | 5 - 90 %, RH, Non-Condensing |
| Power Provided to Connected Device(s) | 20V / 3A (60W) |
| CONNECTIONS | |
| Ports | 2 |
| Side A - Connector 1 | USB C (MALE) |
| Side B - Connector 1 | USB C (FEMALE) |
| Side B - Connector 2 | 3.5MM (FEMALE) |
| FEATURES & SPECIFICATIONS | |
| USB Specification | USB 3.1 Gen 1 (up to 5 Gbps) |
| Audio Specification | Digital Hi-Res Audio |
| Quick Charge Compliant | 2.0 |
| Technology | PD Charging; Stereo Audio |
| STANDARDS & COMPLIANCE | |
| Certifications | RoHS, REACH, CE, FCC, WEEE |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>