

Wireless Charging Stand - 10W Fast Charging, Apple and Samsung Compatible, Black

MODEL NUMBER: U280-Q01ST-BK



Wireless fast-charging stand transfers battery power to your device without connecting a troublesome cable between them.

Features

Wireless Cell Phone Charger Delivers up to 10W for Apple and Samsung Phones Who wants to plug and unplug cords when you just want to charge your cell phone? The U280-Q01ST-BK makes charging more convenient by doing it wirelessly. Just place your Qi-certified device on the charging stand. That's all there is to it. This wireless phone charger even works through most protective phone cases up to 5 millimeters. Note: please remove any magnetic or metal objects from your phone or case before charging. **Compatible with Qi-Certified Cell Phones to Ensure a Safe, Flawless Charge** The U280-Q01ST-BK charges all Qi smartphones from Apple, Sony, LG, Samsung, Nokia and other popular brands in either portrait or landscape orientation. It protects your expensive device from overheating and overcharging that could lead to internal damage. The Smart LED flashes blue to indicate the charging process is underway and changes to a solid blue to let you know your phone is at 100%.

Compact Stand Fits Comfortably on Any Counter, Table or Workspace The portable lightweight stand is just five inches in height and fits easily on your desktop or bedside table. An included USB cable connects the charger to a user-supplied QC USB wall charger or power adapter (QC 2.0 or 3.0 adapter is recommended for high-speed charging).

Highlights

- Charges your Apple, Google or Samsung smartphone wirelessly without a cable
- LED flashes blue during charging and turns solid blue to indicate device is fully charged
- Charges your smartphone through its protective case to avoid the hassle of removing it
- Prevents overheating and overcharging to protect your essential device from damage
- Universally compatible with all Qi-certified smartphones and other devices

Applications

- Transfer power from a wall charger or power adapter to your smartphone's battery without the burden of carrying and connecting extra cabling

System Requirements

- Compatible with all Qi-certified smartphones, including Apple iPhone 11 Pro Max/11 Pro/11/XS Max/XS/XR/8/8 Plus; Samsung S7-S10 Series and Note 8-10 Series; Google Pixel 4 XL/Pixel 4/Pixel 3 XL/Pixel 3; and Nokia 9 PureView/8 Sirocco

Package Includes

- U280-Q01ST-BK Wireless Charging Stand, Black
- USB 2.0 A to USB-C cable, 3 ft.
- Quick Start Guide



Specifications

OVERVIEW	
UPC Code	037332253651
Product Type	Wireless Charger
Charging Form Factor	Pad/Stand
Device Compatibility	Phone; Tablet; Amazon Kindle; Headphones; Watch
Over Current Protection	Yes
INPUT	
Nominal Input Voltage(s) Supported	9V DC
Input Plug Type	USB MICRO-B (FEMALE)
Input Plug Type Detail	USB-A to USB Micro B cable provided
OUTPUT	
Output (Watts)	5W; 7.5W; 10W
Overload Protection	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Blue and Red (Flashes Twice) = Unit Powered On/Low Voltage Reset; Blue (Solid) = Charging; Red (Solid) = Finished Charging/Standby (No Device Charging), Overheating (With Device Charging); Red (Flashing) = Charging Error
CHARGING	
Number of Charging Ports	0
Total Charging Amps	1.1A
USB Power Delivery (PD) Charging Support	No
Charging Method	Wireless
Total Charging Watts	10
Charging Ports Detail	5V/1A (5W); 9V/1.1A (10W)
Charging Port Type	WIRELESS CHARGING COIL
Charging Method Detail	Qi Compatible
PHYSICAL	
Color	Black
Material of Construction	PCB, ABS
Unit Dimensions (hwd / in.)	5.5 x 2.75 x 0.55



Unit Packaging Type	Box
Unit Weight (kg)	0.15
Unit Weight (lbs.)	0.331
ENVIRONMENTAL	
Operating Temperature Range	32 to 95°F (0 to 35°C)
Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Operating Humidity Range	10% to 80% RH
Storage Humidity Range	5% to 95% RH
CONNECTIONS	
Ports	1
Side A - Connector 1	USB Type-C (FEMALE)
Side B - Connector 1	WIRELESS CHARGING COIL
FEATURES & SPECIFICATIONS	
Driver Required	No
Quick Charge Compliant	No
Technology	USB
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	RoHS, REACH, CE, FCC
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>