

DIY Wall 3 Series Dimensions Table

Model Numbers	Diag. Size	Aspect Ratio	Overall Length (A)	View Width (A1)	Wall Hook Distance (A2)	Screen Width (A3)	L/R Border (A4)	Overall Height (B)	View Height (B1)	End Cap Height (B2)	Top Border (B3)	Bottom Border (B4)	Screen Height (B5)
Unit: Inches													
DIYW100H3	100"	16:9	90.3	87.2	49.0	89.2	1.0	59.8	49.0	0.9	4.4	4.4	57.9
DIYW116H3	116"	16:9	104.3	101.1	62.9	103.1	1.0	59.7	56.9	0.9	0.5	0.5	57.9
DIYW135H3	135"	16:9	120.9	117.7	79.5	119.7	1.0	73.6	66.2	0.9	2.7	2.7	71.7
DIYW150H3	150"	16:9	133.9	130.7	92.5	132.7	1.0	79.5	73.5	0.9	2.0	2.0	77.6
Unit: mm													
DIYW100H3	100"	16:9	2294	2214	1244	2265	25	1518	1245	24	113	113	1470
DIYW116H3	116"	16:9	2648	2568	1598	2619	25	1518	1445	24	13	13	1470
DIYW135H3	135"	16:9	3070	2989	2020	3040	25	1868	1681	24	70	70	1820
DIYW150H3	150"	16:9	3400	3321	2350	3372	25	2018	1868	24	51	51	1970

Note: Data error ±1"

The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.

