



Ideal for businesses in need of a mobile check printing solution. **The portability of this unit is its most unique quality**, providing satellite, mobile, and remote office locations with the ability to **print checks on the go**.



Compact & Lightweight

Weighing only 9 pounds, this printer is ideal for travel and can print checks virtually anywhere.



Quality & Reliability

In times of crisis, this inkjet solution provides the quality and reliability to serve your clients.



Efficiency & Security

Eliminate fraud risks associated with theft of preprinted check stock by printing the MICR line and other details at the point of issue.



Captivating User Experience

Easy-to-use control panel with a plug & play setup focus on the importance of user experience.

- Simple mobile printing
- Easy setup
- Long lasting battery
- Perfect for mobile workers printing:
 - Insurance claim checks
 - Payroll or expense checks
 - Realty checks and more...

General Specification

Print Speed: Up to 20ppm AC, Up to 18ppm Battery

First Page Out: 12 Sec from ready mode

Monthly Volume: Up to 500 pages

Input Capacity: 50 Sheets

Network: USB 2.0, Wi-Fi, Wi-Fi Direct

Duplex: Manual (with driver support)

Paper: Letter, Legal, Executive, 8.5 x 13, A4, A5, A6, B5 (JIS)

Warranty: 1 Year return to TROY

PART #	PRINTERS	TRAYS	PAGES	BOXED DIMENSIONS & WEIGHT
01-06200-001	200 Mobile MICR Printer	1	50	20x10x5in / 8lbs (3.6kg)
PART #	TONER	YIELD ¹		BOXED DIMENSIONS & WEIGHT
02-MC2P04A-062	200 Mobile MICR Ink 62	200		3x3x2in / 1lb (.5kg)
02-MC2P05A-062	200 Mobile MICR Ink 62XL	600		3x3x2in / 1lb (.5kg)

1. Page yield based on 5% continuous print coverage