

1 ft Computer Power Cord - IEC 320 EN 60320 C14 to NEMA 5-15R

**Product ID:** PAC100



The PAC100 1ft Computer Power Cord/Cable enables you to use the switched source on your PC to power your monitor or printer.

Expertly designed and constructed of high quality materials, this C14 to NEMA 5-15R cable features one hooded (male) power connector and one computer power (female) connector.

This high quality computer power cable is backed by our Lifetime Warranty.

## Certifications, Reports and Compatibility

## Applications

- Allows monitor or printer to draw power from the switched source on the PC

## Features

- 1x IEC 60320 C14 plug
- 1x NEMA 5-15 receptacle
- Durable construction

---

### Connector(s)

Warranty

Lifetime

Connector A	IEC 60320 C14 Power
Connector B	NEMA 5-15 Power (North America)

---

**Special Notes / Requirements**

Note	UL Listed
------	-----------

---

**Power**

Input Voltage	125 AC
Input Current	10 A

---

**Environmental**

Operating Temperature	-20 to 60 C
Storage Temperature	-20 to 60 C
Humidity	0 to 70%

---

**Physical Characteristics**

Color	Black
Wire Gauge	18 AWG
Cable Length	12.0 in [30.5 cm]
Product Length	12.0 in [30.5 cm]
Product Width	1.4 in [35 mm]
Product Height	1.0 in [25 mm]
Weight of Product	2.5 oz [71.0 g]

---

**Packaging Information**

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	1.4 in [36.0 mm]
Shipping (Package) Weight	2.8 oz [80.0 g]

---

**What's in the**



**Box**

Included in Package      1 Ft. Monitor Power Adaptor

---

***\*Product appearance and specifications are subject to change without notice.***

