

Model 311

Electronic Office Scale CE



- **Accuracy**– 0.1% of full scale
- **Capacity**– 5000 g x 1 g / 11 lb x 0.1 oz
- **Construction**– ABS plastic injection molded case and platter
- **Display**– LCD display with 15 mm / 0.6" high digits
- **Power**– Four AA batteries (included)
- **Operator Keys**– On/Tare, Off, Units
- **Platform Dimension**– 149 mm diameter
5.875" diameter

VALUE IN
WEIGHING

Model 311 Electronic Office Scale

Features

This simple weight-only electronic scale is perfect for letter and small parcel mail to ensure correct postage without overpayment. Includes On/Tare, Off and Units buttons. Displays weight in lb/oz, kg/g. The low profile design is easy to use and store. Uses four AA batteries (included).

Specifications

Capacity: 5000 g / 11 lb

Platform Dimension: 149 mm diameter / 5.875" diameter

Display: LCD display with 15 mm / 0.6" high digits

Keyboard: On/Tare, Off, Unit

Units: Selectable lb/oz and kg/g modes

Power: Four AA batteries (included)

Operating Temperature: 0° C to 40° C / 32° F to 104° F

Packaging Dimension:

274 (L) mm x 204 (W) mm x 58 mm (H)

10.75" L x 8" W x 2.25" H

Shipping Weight: 1 kg / 2 lb

Product Code: 816965001316



a division of Avery Weigh-Tronix, LLC

Brecknell

1000 Armstrong Dr., Fairmont, MN 56031
Toll free: 800-637-0529, Tel: 507-238-8702
Fax: 507-238-8271
e-mail: sales@brecknellscales.com
www.brecknellscales.com



Brecknell

Foundry Lane, Smethwick
West Midlands B66 2LP UK
Tel: +44 (0) 845 246 6717
Fax: +44 (0) 845 246 6718
Email: sales@brecknellscales.co.uk
www.brecknellscales.co.uk

