

MAN & MACHINE

L COOL KEYBOARD



**Closed Deck Keyboard
w/Umbrella Style Keys**

TECHNICAL DATA

FEATURES

- Lockable - Keys lock for workstation cleaning
- Standard quick disconnect cable
- Standard tactile feel
- Clean with any EPA-certified disinfectant
- Standard key pitch
- Full sized keyboard with 104 keys with numeric keypad
- Rugged, durable plastic exterior
- 1-year ltd. warranty



SPECIFICATIONS

- IP 65
- Color: White/Black
- Size: 17.3 x 5.53 x 0.90 (440 x 140.462 x 19.05 mm)
- Weight: 1.17 lb (530.8g)
- Cable length: w/ Extension Cable: 4.9' (1.5m); Cable length w/o Extension Cable: 8.6" (0.22m)
- Storage temperature: 32° to 158° F (0° to 70° C)
- Operating temperature: 32° to 158° F (0° to 70° C)
- Power consumption: 5V/60mA
- Platform: Win, Linux, MAC
- Connection: USB
- Switch rating > 11 million

Sink Rinsable & Wipeable



Short Cable for
Easy Cable Management



THE KEY TO INFECTION CONTROL

3706 West Street • Landover, MD 20785 • 301.341.4900

