

1ft (30cm) Power Extension Cord, Right Angle NEMA 5-15P to NEMA 5-15R, 13A 125V, 16AWG, Black Computer Power Extension Cord, AC Outlet Extension Cable, UL Listed

Product ID: PAC101R1



Save room around the office, maximize power outlet space, and extend the length of your bulky power cords. This flat extension cord lets you do all three.

The low-profile extension cord has a right-angled NEMA 5-15 plug that sits flat against the wall. This lets you save clearance room when plugging in your device behind a cabinet, desk or other piece of furniture. You no longer need to push up against the plug so that your furniture isn't sticking off the wall. This avoids putting strain on the plug and protects it from damage. You can use it to extend any NEMA 5-15 power cord (computer, TV, office lamp, etc.) that needs to be plugged into a power outlet located behind a piece of furniture.

The right-angle power cord also lets you maximize the space on your power strip, surge protector or wall outlet. Since the plug sits to the right of the outlet, the outlet below it or above it isn't blocked which comes in handy when you have to plug in a device with a large, bulky power cord. You can plug the bulky power cord into the receptacle of the extension cord and plug the right-angled plug into the outlet, freeing up another outlet that would have otherwise been blocked.

PAC101R1 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility







Applications

• Extend an existing power cord by up to a foot



Features

- AC POWER EXTENSION CORD: This 1ft (0.3m) Right-Angle 16AWG AC power extension cord with NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office. Indoor use. Rated to carry 125V at 13A
- PERFORMANCE AND SAFETY: UL listed (UL62 & UL817) Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor extension cord made with 100% copper wire This power extension cord is available in other lengths
- SPECS: 1ft (0.3m) AC Power Cord NEMA 5-15R to Right-Angle NEMA 5-15P 16AWG 125V 13A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.33in (8.5mm)
- COMPATIBILITY: PC Power Extension Cord NEMA 5-15P works with North American outlets Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware		
	Warranty	Lifetime
	Number of Conductors	3
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Type	SJT
Connector(s)		
	Connector A	1 - NEMA 5-15 Power (North America)
	Connector B	1 - NEMA 5-15 Power (North America)
Special Notes / Requirements		
	Note	UL Listed
Power		
	Input Voltage	125 AC
	Input Current	13 A
Environmental		
	Operating Temperature	-20C to 60C (-4F to 140F)
	Storage Temperature	-20C to 60C (-4F to 140F)



	Humidity	20~80% RH
Physical Characteristics		
	Color	Black
	Connector Style	Straight to Right Angle
	Wire Gauge	16 AWG
	Cable Length	1.0 ft [0.3 m]
	Product Length	1.0 ft [0.3 m]
	Product Width	0.5 in [12.0 mm]
	Product Height	0.4 in [1.0 cm]
	Weight of Product	3.5 oz [98.0 g]
Packaging Information		
	Package Length	8.8 in [22.4 cm]
	Package Width	7.8 in [19.8 cm]
	Package Height	0.4 in [10.0 mm]
	Shipping (Package) Weight	3.5 oz [100.0 g]
What's in the Box	Included in Package	1 - power cable

^{*}Product appearance and specifications are subject to change without notice.