

Evanescence Series Dimensions Table (Below Ceiling Installation)

Unit: mm																						
Model Number	Diagonal Size & Aspect Ratio	Overall Length (A)	View Width (A1)	L/R black masking (A2)	Screen Width	Weight Bar Length (A3)	Housing Length (A4)	A5	Top of screen case to bottom of screen (B)	View Height (B1)	Top Black Masking (B2)	Bottom Border (B3)	Case Height (B4)	C	C1	C2	D	D1	D2	D3	Control box height	
IHOME126VW2-E8	126"(4:3)	2830	2561	50	2661	2761	2771	2794	2347	1920	203	98	118	147	98	119	1300	2400	130	80	40	
IHOME90HW2-E24	90"(16:9)	2250	1993	38	2069	2182	2192	2215	1948	1120	610	98	118	147	98	119	1300	2400	130	80	40	
IHOME106HW2-E18	106"(16:9)	2606	2347	50	2447	2535	2545	2570	1996	1321	457	98	118	147	98	119	1300	2400	130	80	40	
IHOME106H2-E14-AUHD	106"(16:9)	2605	2347	50	2447	2535	2545	2570	1870	1320	356	76	118	148	98	120	1300	2400	130	80	40	
IHOME112HW2-E16	112"(16:9)	2738	2480	50	2580	2667	2677	2703	2022	1397	406	98	118	147	98	119	1300	2400	130	80	40	
IHOME126HW2-E20	126"(16:9)	3048	2790	50	2890	2977	2987	3012	2296	1570	508	98	118	147	98	119	1300	2400	130	80	40	
IHOME126H2-E12-AUHD	126"(16:9)	3048	2790	50	2890	2978	2988	3013	2068	1569	305	76	118	148	98	120	1300	2400	130	80	40	
IHOME114XW2-E20	114"(16:10)	2715	2456	50	2556	2644	2654	2680	2261	1534	508	98	118	147	98	119	1300	2400	130	80	40	
IHOME120XW2-E18	120"(16:10)	2842	2585	50	2685	2774	2784	2809	2291	1615	457	98	118	147	98	119	1300	2400	130	80	40	
IHOME132XW2-E12	132"(2:35:1)	3101	2844	50	2944	3033	3043	3066	2301	1778	305	98	118	147	98	119	1300	2400	130	80	40	
IHOME110C-E24	110"(2.35:1)	2830	2571	50	2671	2761	2771	2794	1923	1095	610	98	118	147	98	119	1300	2400	130	80	40	
IHOME140H2-E6-AUHD	140"(16:9)	*	*	*	*	*	*	*	*	*	*	*	*	*Installation method not available				1300	2400	130	80	40
Unit: Inches																						
IHOME126VW2-E8	126"(4:3)	111.4	100.8	2.0	104.8	108.7	109.1	110.0	92.4	75.6	8.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME90HW2-E24	90"(16:9)	88.6	78.5	1.5	81.5	85.9	86.3	87.2	76.7	44.1	24.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME106HW2-E18	106"(16:9)	102.6	92.4	2.0	96.3	99.8	100.2	101.2	78.6	52.0	18.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME106H2-E14-AUHD	106"(16:9)	102.6	92.4	2.0	96.3	99.8	100.2	101.2	73.6	52.0	14.0	3.0	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME112HW2-E16	112"(16:9)	107.8	97.6	2.0	101.6	105.0	105.4	106.4	79.6	55.0	16.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME126HW2-E20	126"(16:9)	120.0	109.8	2.0	113.8	117.2	117.6	118.6	90.4	61.8	20.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME126H2-E12-AUHD	126"(16:9)	120.0	109.8	2.0	113.8	117.2	117.6	118.6	81.4	61.8	12.0	3.0	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME114XW2-E20	114"(16:10)	106.9	96.7	2.0	100.6	104.1	104.5	105.5	89.0	60.4	20.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME120XW2-E18	120"(16:10)	111.9	101.8	2.0	105.7	109.2	109.6	110.6	90.2	63.6	18.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME132XW2-E12	132"(16:10)	122.1	112.0	2.0	115.9	119.4	119.8	120.7	90.6	70.0	12.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME110C-E24	110"(2.35:1)	111.4	101.2	2.0	105.2	108.7	109.1	110.0	75.7	43.1	24.0	3.9	4.6	5.8	3.9	4.7	51.2	94.5	5.1	3.1	1.6	
IHOME140H2-E6-AUHD	140"(16:9)	*	*	*	*	*	*	*	*	*	*	*	*	*Installation method not available				51.2	94.5	5.1	3.1	1.6

Note: Data Error may be ±1"

The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.

