

6ft (1.8m) DisplayPort to VGA Cable - Active DisplayPort to VGA Adapter Cable - 1080p Video - DP to VGA Monitor Cable - DP 1.2 to VGA Converter - Latching DP Connector

Product ID: DP2VGAMM6



The DP2VGAMM6 6ft DisplayPort to VGA (M-M) Cable lets you connect a VGA capable display to a DisplayPort video card/source. The cable provides a connection distance of 6 feet and features a male VGA connector and a male DisplayPort connector.

The DisplayPort to VGA adapter cable supports high bandwidth video transmissions, easily delivering monitor resolutions up to 1920x1200 or HDTV resolutions up to 1080p - allowing you to take full advantage of your VGA display, while using a cutting edge DisplayPort video source.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Keep your existing VGA display to use with newer DisplayPort monitors
- The DisplayPort to VGA cable allows for an easy and hassle free connection to any VGA monitor or projector

Features

- **DISPLAYPORT TO VGA CABLE:** 6ft (1.8m) DisplayPort 1.2 (HBR2) adapter cable lets you connect a single VGA display supporting 2048x1280, 1920x1200 & 1920x1080 (1080p) at 60Hz; EDID & DDC pass-through ensure compatibility between source & display
- **COMPATIBILITY:** Active digital to analog converter supports DP or DP++ source w/ standard DP connector incl workstations, desktops (AMD/Nvidia), laptops, small form factor computers & docking stations

- **INTEGRATED DISPLAY CABLE:** Adapter cable has a slim & flexible design w/ adapter chip built into VGA connector reducing clutter & providing a tidy install at your desk workstation in the office or home office
- **LATCHING DISPLAYPORT & SCREW LOCKING VGA:** Latching DP connector ensures a solid host connection, and chip built into VGA connector minimizes signal loss Supports VGA screw locking cable to prevent cable from coming loose or accidental disconnection
- **EASY TO USE:** With no software or drivers required, the DP to VGA video converter cable/cord works with any OS including macOS, Windows & Ubuntu DP Source to VGA Monitor/Display/Projector DisplayPort Male to VGA Male Cable

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	DisplayPort - 1.2
AV Output	VGA
Audio	No
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride

Performance

Maximum Cable Length	6.0 ft [1.8 m]
Maximum Digital Resolutions	1920x1200 / 1080p
Audio Specifications	VGA - No Audio Support

Connector(s)

Connector A	DisplayPort (20 pin)
Connector B	VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%-85%RH

Physical



Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.4 in [35.0 mm]
Product Height	5.6 ft [1.7 m]
Weight of Product	3.7 oz [106.0 g]

Packaging Information

Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	4.0 oz [114.0 g]

What's in the Box

Included in Package	6 ft DisplayPort to VGA Cable - M/M
---------------------	-------------------------------------

**Product appearance and specifications are subject to change without notice.*

