

6 ft Computer Power Cord - C19 to C20

Product ID: PXTC19C206



This 6ft Power Cord is a compact C19 to C20 computer cable that is designed to work with racks and Power Distribution Units.

Backed by StarTech.com's Lifetime Warranty, this 6ft computer power cord is expertly designed for longevity, and is constructed of only the highest quality of materials.

Certifications, Reports and Compatibility

Applications

Features

- Rated to carry 250V at 13A
- 16 AWG wire

Connector(s)

Warranty	Lifetime
Connector Type(s)	IEC 60320 C19 Power IEC 60320 C20 Power

Special Notes /

Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	250 AC
Input Current	13 A

Environmental

Operating Temperature	60C
-----------------------	-----

Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Weight of Product	10.6 oz [301 g]

Packaging Information

Package Length	11.4 in [29 cm]
Package Width	5.7 in [14.5 cm]
Package Height	2.4 in [60 mm]
Shipping (Package) Weight	10.9 oz [308 g]

What's in the Box

Included in Package	6 ft Computer Power Cord - C19 to C20
---------------------	---------------------------------------

****Product appearance and specifications are subject to change without notice.***

