



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Installation guide Rack mounting brackets Safety guide
--------------------	--

Physical

Colour	Black
Depth	4.6 cm
Height	179.7 cm
Net weight	5.55 kg
Width	5.5 cm

Input

[In] rated current	16 A
Permissible voltage	100...240 V
Communication port protocol	SNMP Redfish
Input current limits	20 A
Load capacity	3300 VA
Network frequency	50/60 Hz
Plug standard	IEC 60320 L6-20P
Input voltage	200 V

Output

Number of power socket outlets	21 C13/C15 3 C19/C21
--------------------------------	-------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

Product certifications	FCC part 15 class A PSE
------------------------	----------------------------

Environmental

Ambient air temperature for operation	-5...60 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Batteries & Runtime

Communication network type	10/100/1000BASE-T Wi-Fi (optional)
----------------------------	---------------------------------------

Packing Units

Package 1 Weight	7.86 kg
Package 1 Height	200.2 cm
Package 1 width	16.5 cm
Package 1 Length	11.4 cm
Number of Units in Package 3	48

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------
