

3ft Micro USB Cable - A to Micro B

Product ID: UUSBHAUB3



The UUSBHAUB3 3-foot USB A to Micro USB cable features one USB 'A' male connector, and one 'Micro-B' male connector, providing a high quality connection to USB 2.0 mobile devices (such as BlackBerry or Android-based cellular phones, digital cameras, PDA's, Tablet PC devices and GPS systems) that use a Micro USB connector to a USB capable computer for everyday tasks such as data synchronization and file transfers.

This high quality cable is backed by StarTech.com's Lifetime Warranty to ensure dependable, long-lasting connections between Micro USB and USB devices.

Certifications, Reports and Compatibility

Applications

• An ideal replacement cable for connecting mobile devices to a USB capable computer

Features

- Supports high speed data transfer rates up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding
- High quality USB 'A' and USB 'Micro-B'connectors
- Durable PVC construction

Hardware



Warranty Lifetime

Connector Plating Nickel

Cable Jacket Material PVC - Polyvinyl Chloride

Cable Shield Material Aluminum-Mylar Foil with Braid

Performance

Type and Rate USB 2.0 - 480 Mbit/s

Connector(s)

Connector A USB Type-A (4 pin) USB 2.0

Connector B USB Micro-B (5 pin)

Environmental

Operating Temperature -20C to 60C (-4F to 140F)

Storage Temperature -10C to 30C (14F to 86F)

Humidity 30%-75% RH

Physical Characteristics

Color Black

Wire Gauge 24/30 AWG

Cable Length 36.0 in [91.4 cm]

Product Length 36.0 in [91.4 cm]

Product Width 0.0 in [0.0 mm]

Product Height 0.0 in [0.0 mm]

Weight of Product 1.0 oz [29.0 g]

Packaging Information

Package Length 8.9 in [22.5 cm]

Package Width 4.9 in [12.5 cm]

Package Height 0.0 in [0.1 mm]

Shipping (Package) 1.2 oz [35.0 g]



	ht

What's in the Box

Included in Package 3ft Micro USB Cable - A to Micro B

^{*}Product appearance and specifications are subject to change without notice.