



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Salerno LED Flush Mount SALF Series

Features

Simplistic ceiling light can be used in various applications including corridors, baths and public spaces.
Fixture mounts to standard junction box (not included)

Construction

Fabricated metal housing and canopy.
The canopy fits over a standard junction box.
Power supply connections must be made inside a junction box (not included).

Finish

Polished Chrome finish.

Diffuser

White glass diffuser.

Electrical

Input 120-277 VAC 60 HZ.
Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers.
TRIAC and ELV dimming only at 120VAC.

LED

Integrated LED modules capable of producing:
17W, 1159 delivered lumens
29W, 1776 delivered lumens
Adjustable Choice 3000K, 3500K, 4000K (CCT).
Rated for 50,000 Hrs., 90 CRI.

Options

Battery back-up (add BB to end of model #).

Certification

All fixtures are cETLus listed for indoor damp locations.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 year from date of purchase.

Specifications and dimensions
subject to change without notice.

Ordering Information:

Polished Chrome	LED	Delivered Lumens	Adjustable CCT	DIA.	D
SALF13LAJUDPC	17W	1159	3000K/3500K/4000K	13-1/2"	5-1/2"
SALF16LAJUDPC	29W	1776	3000K/3500K/4000K	16-1/4"	5-1/2"

3in1 color temperature
3000K/3500K/4000K

