



LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

Delany LED Flush Mount MIDF Series

Features

This Delany LED flush mount is a highly decorative style fixture providing beauty and light to any room. An excellent alternative solution to incandescent or CFL fixture with long lasting and energy saving LED technology. Ideal use for general lighting in indoor residential, commercial, and hospitality applications. Fixture must be mounted to a standard junction box (not included) on a ceiling. Available in multiple sizes.

Construction

A 20-gauge steel pan made by stamping process and plated to provide a long lasting finish with matching 4 metal decorative side trims. A side diffuser is made of 0.188" thick acrylic with inside sand blasted and painted off white with outside being grooved vertically and evenly spaced to create a prism effect. The bottom flat white diffuser is simply attached to the housing with round metal finial in matching finish. Power supply connections must be made inside a junction box (not included).

Finish

Satin nickel.

Diffuser

0.090" thick flat white acrylic on bottom.
0.188" thick round white acrylic on side.

Electrical

Input 120-277 VAC 60 Hz.
Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers.
TRIAC and ELV dimming only at 120VAC.

LED

Integrated LED modules capable of producing:
16" - 30W, 2400 source lumens
22" - 42W, 3200 source lumens
Adjustable Choice 3000K, 3500K, 4000K (CCT).
Rated for 50,000 Hrs. 90 CRI.

Certification

All fixtures are cETLus listed for indoor damp locations.

Warranty

Limited warranty: This fixture is free from defects in materials and workmanship for a period of 5 years from date-of-purchase.

Specifications and dimensions
subject to change without notice.

Ordering Information:

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	D
MIDF1624LAJUDSN	30W	2400	3000K/3500K/4000K	16-1/4"	5-3/4"
MIDF2232LAJUDSN	42W	3200	3000K/3500K/4000K	22-1/4"	5-1/2"



3in1 color temperature
3000K/3500K/4000K

