

Style #1284FR-OZ-RD-CID

- > 100% polyester flame-retardant mesh safety vest with 2 radio clip holders, 1 clear ID holder and high-visibility reflective tape over shoulders and around torso

Features

- > **Binding:** Hi-vis orange polyester
- > **Material:** 100% polyester mesh fabric
- > **Color:** Hi-vis orange
- > **Standard:** ANSI/ISEA 107
- > **Class:** Type R, Class 2
- > **Closure:** Zipper front closure
- > **Tape:** 2" silver reflective tape
- > **Pockets:** 5 Pockets - 1 upper left chest pocket, 2 exterior waist pockets, 2 interior waist pockets



(Front)



(Back)



- > **Flame-Retardant Properties:** The treated fabric on this vest has been tested under test method D6413 and will self-extinguish when caught on fire. (After-flame is less than 2.0 second on average; char length is less than 6" on average.) This vest should never be used where an arc flash or flash fire is present.

ironwear®

ITEM#: 1284FR-OZ-RD-CID
 SIZE: MD
 Class 2
 Meets ANSI/ISEA 107-(year)
 100% POLYESTER
 Care Instructions:
 Machine Wash warm, Tumble dry low, Do not bleach, Do not iron, Do not dry clean



RN95108
 MADE IN CHINA

The fabric in this garment has been tested under ASTM test method D6413 and will Self-Extinguish when caught on fire. Self Extinguishing properties will diminish with washing

This garment should never be used when an arc flash or flash fire hazard is present. This garment is not flame resistant as defined by ANSI/ISEA 107-(year) Section 10.5



Type R
 Class 2
 NOT FR

Measurements

Size	SM	MD	LG	XL	2XL	3XL	4XL	5XL	6XL
Width (in)	22	23.5	25	26.5	28	29.5	31	32.5	34
Length (in)	26	27	28	29	30	31	32	33	34

Packaging

Packaging	1 each per poly bag, 50 each per case								
Unit	Each								
Case Pack	50								
Case Weight (lb)	19.84	22.05	22.05	24.25	26.46	28.66	28.66	29.2	30.87
Case Dimensions (in)	16.54 x 11.02 x 11.42		16.54 x 11.02 x 12.6		16.54 x 11.02 x 13.78		16.54 x 11.02 x 14.57		