

Style #3975-GO

Raptor - Non Vented


- > Safety Helmet
- > Ratchet with 4 Point Suspension
- > Chin Strap
- > Meets ANSI/ISEA Z89.1-2014 for:
 - Type II (For protection to a blow to the top and sides of head).
 - Class E (Electrical, tested to 22,000 V)
 - HT (High temperature up to 120° f +/- 3.6° f)
 - LT (Low temperature above -22° f +/- 3.6° f)



(Side)



(Front with Chin Strap)



(Inside Suspension)



(Back with Ratchet)

Description

- > **Material:** PC & ABS
(Polycarbonate & Acrylonitrile butadiene styrene)
- > **Color:** Gold
- > **Size:** 6.5 - 8

Packaging

- > **Packaging:** 1 each / box, 12 / shipping carton
- > **Unit:** each
- > **Case Pack:** 12
- > **Case Weight:** 12lb / 9kg
- > **Case Dimensions:** 27.5" x 22.8" x 21.7
- > **Case Dimensions:** 70cm x 58cm x 55cm

Color Options



W - White Y - Yellow R - Red LB - Light Blue P - Pink O - Orange G - Grey DG - Dark Green PR - Purple BL - Black M - Maroon N - Navy



GO - Gold S - Silver B - Blue HO - High Visibility Orange LBU - Light Buff L - Lime T - Tan REB - Robin's Egg Blue LGR - Light Grey BR - Brown LG - Lime Green