

Stock Code: **28022-3C-ORB/LGR**

Collection: Flute

### PRODUCT INFORMATION

Base: 28022 (Cord) Parent: 28022-3C  
Mounting Type: Ceiling UPC: 641594209198  
Finish: Oil Rubbed Bronze  
Diffuser: Lime Green

### PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length
Width:	Width:
Diameter	Diameter:
Height: 6.5"	Height: 1.25"
Extension:	
Overall Height: 8-151.5"	

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Metal  
Diffuser Material: Glass  
Lamping Type: E-26 (Replaceable LED Jbox: Standard  
Lamping Base: E-26 Lamp Wattage: 10 W  
Lamp Quantity: 1 Total Wattage: 10 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating Dry  
Certification: UL (US/Canada) Listed  
ADA Compliant: No Energy Star: No  
JA8 Compliant: Yes Emergency Lighting: No  
Marine Grade: No Warranty: 1 Year

#### PHOTOMETRICS

Dimmable: Yes Nominal Lumens 800 Lm  
CRI: 90 Delivered Lumens: N/A  
CCT: 3000K  
Recommended Dimmers:  
(MLV)COOPER Aspire 9530SW; (TRIAC)LEGRAND Titan  
CD703-PW; (ELV)LUTRON Skylark SELV-300P

#### Additional Notes:

Brushed steel finish paired with 12 feet of clear cord

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Type: \_\_\_\_\_


Quantity: \_\_\_\_\_

Notes: \_\_\_\_\_



LINE DRAWING

IES FILE



In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice. 11/2/2022 28022-3C-ORB\_LGR.pdf

