

Stock Code: **31002-BS/OPL**

Collection: Vail

### PRODUCT INFORMATION

Base: 31002 Parent: 31002  
Mounting Type: Wall UPC: 641594076035  
Finish: Brushed Steel  
Diffuser: Opal

### PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length 25.75"
Width: 30.25"	Width: 3"
Diameter	Diameter:
Height: 4.25"	Height: 1.5"
Extension: 3.25"	
Overall Height:	

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Metal  
Diffuser Material: Glass  
Lamping Type: Bi-Pin (Fluorescent) Jbox: Standard  
Lamping Base: Bi-Pin Lamp Wattage: 24 W  
Lamp Quantity: 1 Total Wattage: 24 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating Damp  
Certification: UL (US/Canada) Listed  
ADA Compliant: Yes Energy Star: No  
JA8 Compliant: No Emergency Lighting: No  
Marine Grade: No Warranty: 1 Year

#### PHOTOMETRICS

Dimmable: No Nominal Lumens 1750 Lm  
CRI: N/A Delivered Lumens: N/A  
CCT: 3000K  
Recommended Dimmers:


#### Additional Notes:

Fully adjustable floating canopy included; Horizontal and Vertical Mounting; Custom Finish 5 Piece Minimum Order Quantity

Project Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Type: \_\_\_\_\_  
Quantity: \_\_\_\_\_  
Notes: \_\_\_\_\_



#### LINE DRAWING



#### IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice. 12/15/2022 31002-BS\_OPL.pdf

