

Stock Code: **52031LEDDL-BS/OPL**

Collection: Comet

PRODUCT INFORMATION

Base: 52031 Parent: 52031LEDDL
Mounting Type: Ceiling UPC: 641594216493
Finish: Brushed Steel
Diffuser: Opal

PRODUCT MEASUREMENTS

| FIXTURE | BACKPLATE / CANOPY |
|-----------------|--------------------|
| Length: 71" | Length |
| Width: 4.5" | Width: |
| Diameter | Diameter: 4.5" |
| Height: 13.25" | Height: 1.25" |
| Extension: | |
| Overall Height: | |

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

Frame Material: Metal
Diffuser Material: Glass
Lamping Type: GU-10 (Replaceable LE Jbox: Standard
Lamping Base: GU-10 Lamp Wattage: 5.5 W
Lamp Quantity: 5 Total Wattage: 27.5 W
Voltage: 120v Lamps Included: Yes

QUALIFICATIONS

Location Rating Dry
Certification: ETL (US/Canada) Listed
ADA Compliant: No Energy Star: No
JA8 Compliant: No Emergency Lighting: No
Marine Grade: No Warranty: 1 Year

PHOTOMETRICS

Dimmable: Yes Nominal Lumens 2500 Lm
CRI: 83 Delivered Lumens: N/A
CCT: 3000K
Recommended Dimmers:
(TRIAC)LUTRON Toggler TG-600P; (TRIAC)LEVITON Surslide 6631; (TRIAC)LUTRON Skylark S-600 or S-600P;
(TRIAC)LEVITON Trimatron 6684; (TRIAC)LUTRON Diva DVCL-153P; (TRIAC)LUTRON Skylark S-603PG

Additional Notes:

Sloped ceiling adapter included; Custom Finish 100 Piece Minimum Order Quantity

Project Name: _____

Location: _____


Type: _____

Quantity: _____

Notes: _____



LINE DRAWING



IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: _____

Print Name _____ Date: _____

Toll Free 800-828-5483 www.AccessLighting.com

14410 Myford Road, Irvine, CA 92606

