

Stock Code: **62340LEDD-MSS/SMAMB**

Collection: Dor

### PRODUCT INFORMATION

Base: 62340 Parent: 62340LEDD  
Mounting Type: Ceiling UPC: 641594219326  
Finish: Mirrored Stainless Steel  
Diffuser: Smoked Amber

### PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length
Width:	Width:
Diameter 8"	Diameter:
Height: 8.5"	Height:
Extension:	
Overall Height: 10-129"	

### TECHNICAL SPECIFICATIONS

#### SPECIFICATIONS

Frame Material: Stainless Steel  
Diffuser Material: Glass  
Lamping Type: E-26 (Replaceable LED Jbox: Standard  
Lamping Base: E-26 Lamp Wattage: 9.5 W  
Lamp Quantity: 1 Total Wattage: 9.5 W  
Voltage: 120v Lamps Included: Yes

#### QUALIFICATIONS

Location Rating Dry  
Certification: UL (US/Canada) Listed  
ADA Compliant No Energy Star: No  
JA8 Compliant: No Emergency Lighting: No  
Marine Grade: No Warranty: 1 Year

#### PHOTOMETRICS

Dimmable: Yes Nominal Lumens 800 Lm  
CRI: 84 Delivered Lumens: N/A  
CCT: 3000K  
Recommended Dimmers:  
(ELV)LUTRON Skylark SELV-300P; (TRIAC)LEGRAND Titan CD703-PW; (MLV)COOPER Aspire 9530SW

#### Additional Notes:

10 feet of clear coated cord included

Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Type: \_\_\_\_\_

Quantity: \_\_\_\_\_

Notes:



LINE DRAWING

IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: \_\_\_\_\_

Print Name \_\_\_\_\_ Date: \_\_\_\_\_

Toll Free 800-828-5483 [www.AccessLighting.com](http://www.AccessLighting.com)

14410 Myford Road, Irvine, CA 92606

