

Stock Code: **62495LEDD-CH/OPL**

Collection: Atomiser

PRODUCT INFORMATION

Base: 62495 Parent: 62495LEDD
Mounting Type: Wall UPC: 641594219074
Finish: Chrome
Diffuser: Opal

PRODUCT MEASUREMENTS

FIXTURE	BACKPLATE / CANOPY
Length:	Length
Width: 43"	Width:
Diameter	Diameter:
Height: 14.5"	Height:
Extension:	
Overall Height: 16-52"	

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

Frame Material: Stainless Steel
Diffuser Material: Glass
Lamping Type: SSL (Dedicated LED) Jbox: Standard
Lamping Base: SSL Lamp Wattage: 5 W
Lamp Quantity: 5 Total Wattage: 25 W
Voltage: 120v Lamps Included: Yes

QUALIFICATIONS

Location Rating Damp
Certification: UL (US/Canada) Listed
ADA Compliant No Energy Star: No
JA8 Compliant: No Emergency Lighting: No
Marine Grade: No Warranty: 5 Year

PHOTOMETRICS

Dimmable: Yes Nominal Lumens 2000 Lm
CRI: 90 Delivered Lumens: N/A
CCT: 3000K
Recommended Dimmers:
(ELV)LUTRON Skylark SELV-300P; (ELV)LUTRON Diva DVELV-300P; (ELV)LUTRON Maestro CL MACL-153M; (ELV)LUTRON Diva DVELV-303P; (ELV)LEVITON Viviza (Decora style) VPE06-1LZ; (ELV)LEVITON Decora DSE06-10Z

Additional Notes:

6, 16, and 22-inch down rods included; 10 feet of clear coated cord included

Project Name: _____

Location: _____

Type: _____

Quantity: _____

Notes:



LINE DRAWING

IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: _____

Print Name _____ Date: _____

Toll Free 800-828-5483 www.AccessLighting.com

14410 Myford Road, Irvine, CA 92606

