

Stock Code: **63814-18-CH/OPL**

Collection: Sydney

PRODUCT INFORMATION

Base: 63814 Parent: 63814-18
Mounting Type: Wall UPC: 641594215533
Finish: Chrome
Diffuser: Opal

PRODUCT MEASUREMENTS

| FIXTURE | BACKPLATE / CANOPY |
|-----------------|--------------------|
| Length: | Length |
| Width: 27.25" | Width: |
| Diameter | Diameter: |
| Height: 6.5" | Height: |
| Extension: 5" | |
| Overall Height: | |

TECHNICAL SPECIFICATIONS

SPECIFICATIONS

Frame Material: Metal
Diffuser Material: Glass
Lamping Type: G9 (Halogen) Jbox: Standard
Lamping Base: G9 Lamp Wattage: 40 W
Lamp Quantity: 4 Total Wattage: 160 W
Voltage: 120v Lamps Included: Yes

QUALIFICATIONS

Location Rating: Damp
Certification: UL (US/Canada) Listed
ADA Compliant: No Energy Star: No
JA8 Compliant: No Emergency Lighting: No
Marine Grade: No Warranty: 1 Year

PHOTOMETRICS

Dimmable: Yes Nominal Lumens: 2000 Lm
CRI: N/A Delivered Lumens: N/A
CCT: 2700K
Recommended Dimmers:
(TRIAC) Any Standard Dimmer

Additional Notes:

Project Name: _____

Location: _____

Type: _____

Quantity: _____

Notes:



LINE DRAWING

IES FILE

In addition to Access Lighting's purchase and warranty terms and conditions, by signing below or placing an order, you agree that you are authorized to bind the entity placing any order and acknowledge the following: All of sizes and measurements are approximate and all images are for illustrative purposes only. In the event of an inconsistency, the "Product Measurements" section controls. There also may be slight differences in the colors and designs compared to the displayed and printed images.

Signature: _____

Print Name _____ Date: _____

Toll Free 800-828-5483 www.AccessLighting.com

14410 Myford Road, Irvine, CA 92606

The information is subject to change without notice. 9/27/2022 63814-18-CH_OPL.pdf

