



ACK60ELSTW



40" x 58.88" x 23.5" (H x W x D)

60 inch wide all-in-one kitchenette with 4-burner 220V smooth-top electric range, refrigerator-freezer sink, cutting board and cutlery storage, and a storage cabinet

Highlights:

- Complete all-in-one convenience with a refrigerator-freezer, electric range, sink, and storage compartment in just 60"
- Includes REX2051WRT 4-burner smooth-top electric range
- Includes CP34W refrigerator-freezer

Product Features:

Complete one-piece kitchenette	All-in-one kitchen is built with virtually everything you need for meal preparation
2-door refrigerator-freezer included	CP34W is packaged inside the kitchenette. This 3.2 cu.ft. ENERGY STAR certified refrigerator includes adjustable glass shelves, door storage, and a freezer compartment
Sink and faucet	Stainless steel sink with ready-to-use faucet included
Electric range included	REX2051WRT is packed with the kitchenette. This 220V electric smooth top range includes four 6 1/2" 1200W elements, 2.3 cu.ft. oven with adjustable racks, oven window, and interior lighting
Push-to-turn knobs	Range knobs require a small amount of force to turn the elements on, helping to prevent accidents
Indicator lights	Operating indicators light up to show which burner is in use for added safety
One piece stainless steel countertop	Easy-to-clean surface with a professional look
Removable cutting board surface	Plastic cutting board provides a durable, easy-to-clean space for food preparation
Cutlery bin	Located under the cutting board, allows for easy storage of cutlery and utensils



ACK60ELSTW Specifications:

Overview	
Height of Cabinet	40.0" (102 cm)
Width	58.88" (150 cm)
Depth	23.5" (60 cm)
Depth with door at 90°	44.25" (112 cm)
Capacity	3.2 cu.ft. (91 L)
Defrost Type	Cycle
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Other Energy Info	40 amp range/1.1 amp refrigerator
Weight	230.0 lbs. (104 kg)
Shipping Weight	270.0 lbs. (122 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101075488
Kitchenette	
Refrigerator Included	CP34W
Refrigerator Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Shelf Type	Glass
Shelf Qty	1
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Full Door Shelves	2
Can Storage	Yes
Thermostat Type	Dial
Interior Light	Yes
Refrigerant Type	R600a
Refrigerant Amount	1.16 oz.
High Side PSI	250.0
Low Side PSI	88.0

Cooking Type	Smooth-Top Range
Number of Burners	4
Cooktop Controls	Dial
Range Included	REX2051WRT
Oven Included	Yes

