



ACK60GASW



42" x 58.63" x 23.63" (H x W x D)

60 inch wide all-in-one kitchenette with 115V 4-burner gas range, refrigerator-freezer, sink, cutting board and cutlery storage, and a storage cabinet

Highlights:

Complete all-in-one convenience with a refrigerator-freezer, gas range, sink, and storage compartment in just 60"

Includes RG200WS 4-burner gas range

Includes CP34W refrigerator-freezer

Product Features:

Complete one-piece kitchenette	All-in-one kitchen is built with virtually everything you need for meal preparation
2-door refrigerator-freezer included	CP34W is packaged inside the kitchenette. This 3.2 cu.ft. ENERGY STAR certified refrigerator includes adjustable glass shelves, door storage, and a freezer compartment
Sink and faucet	Stainless steel sink with ready-to-use faucet included
Gas range included	RG200WS is packed with the kitchenette. This 115V gas range includes four sealed burners (1-12000 BTU, 2-9500BTU, 1-5000 BTU) with cast iron grates, 2.3 cu.ft. oven with adjustable racks, and is LP convertible (kit included)
Push-to-turn knobs	Range knobs require a small amount of force to turn the elements on, helping to prevent accidents
Sealed burners	Quality burners ensure lasting durability and easier cleanup
Continuous grates	Two sets of grates are removable for easy cleaning, with solid construction to support large pots and pans
One piece stainless steel countertop	Easy-to-clean surface with a professional look
Removable cutting board surface	Plastic cutting board provides a durable, easy-to-clean space for food preparation



ACK60GASW Specifications:

Overview	
Height of Cabinet	42.0" (107 cm)
Width	58.63" (149 cm)
Depth	23.63" (60 cm)
Depth with door at 90°	43.25" (110 cm)
Capacity	3.2 cu.ft. (91 L)
Defrost Type	Cycle
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Other Energy Info	1.1 amp refrigerator
Voltage/Frequency	115 V AC/60 Hz
Weight	280.0 lbs. (127 kg)
Shipping Weight	320.0 lbs. (145 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101075501

Kitchenette	
Refrigerator Included	CP34W
Refrigerator Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Shelf Type	Glass
Shelf Qty	1
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Full Door Shelves	2
Can Storage	Yes
Thermostat Type	Dial
Interior Light	Yes
Refrigerant Type	R600a
Refrigerant Amount	1.16 oz.
High Side PSI	250.0
Low Side PSI	88.0
Cooking Type	Gas Range
Number of Burners	4

Cooktop Controls	Dial
LP Convertible	Yes
Range Included	RG200WS
Oven Included	Yes

