



# C60EL



40" x 59.18" x 24" (H x W x D)

60" wide all-in-one kitchenette with two coil burners, a cycle defrost refrigerator-freezer, sink, and storage cabinets; replaces C60

### Highlights:

One-piece kitchenette in 60" width and convenient 24" depth

Deluxe CT661W refrigerator-freezer includes adjustable glass shelves, a crisper drawer, wine shelf, and door storage

Perfect in small quarters or as a temporary kitchen

### Product Features:

Two electric burners	120V coil elements for easy cooking
One piece stainless steel countertop	Easy to clean and built to last
Sink and faucet	Stainless steel sink built into the unit
Storage compartments	Two large cabinets with shelves lets you store dry goods behind a door
Refrigerator-freezer included	Includes SUMMIT CT661W, a refrigerator-freezer with dual evaporator cooling, adjustable glass shelves, a crisper, and more
Ships fully assembled	Base model comes in one box. Just slide the refrigerator-freezer into its opening and plug in
100% CFC free	Environmentally friendly design without ozone-damaging chemicals



## C60EL Specifications:

Overview	
Height of Cabinet	40.0" (102 cm)
Width	59.18" (150 cm)
Depth	24.0" (61 cm)
Depth with door at 90°	44.25" (112 cm)
Capacity	5.1 cu.ft. (144 L)
Defrost Type	Cycle
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	25.0
Voltage/Frequency	115 V AC/60 Hz
Weight	220.0 lbs. (100 kg)
Shipping Weight	285.0 lbs. (129 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Kitchenette	
Refrigerator Included	CT661W
Refrigerator Door Swing	RHD
Reversible	Yes
Adjustable Shelves	Yes
Shelf Type	Glass
Shelf Qty	3
Crisper Qty	1
Crisper Finish	Transparent
Crisper Cover	Glass
Full Door Shelves	3
Thermostat Type	Dial
Interior Light	Yes
Refrigerant Type	R600a
Refrigerant Amount	0.92 oz.
Cooking Type	Coil Cooktop
Number of Burners	2
Cooktop Controls	Dial
Interior Height 1	19.5" (50 cm)
Interior Width 1	20.5" (52 cm)

Interior Depth 1	17.0" (43 cm)
Interior Height 2	5.0" (13 cm)
Interior Width 2	19.0" (48 cm)
Interior Depth 2	11.5" (29 cm)
Compressor Step Height	7.0" (18 cm)
Compressor Step With	20.5" (52 cm)
Compressor Step Depth	5.0" (13 cm)
Sink Height	5.88" (15 cm)
Sink Width	16.75" (43 cm)
Sink Depth	14.88" (38 cm)

